SMT Power Inductors

Flat Coils - PG0426 Series









Meight: 3.2mm Max

Footprint: 7.5mm x 7.0mm Max

© Current Rating: 60Apk

Inductance Range: 0.1μH to 1.5μH

Migh temperature core material, no thermal

aging below 150°C

Electrical Specifications @ 25°C - Operating Temperature -40°C to +130°C¹						
Part Number	Inductance @ Irated (μΗ±20%)	DCR (m\O)		Saturation ²	Heating ³	Core Loss ⁴
		ТҮР	MAX	Current Isat (A)	Current l oc (A)	Factor K2
PG0426.101NL	0.10	1.3	1.5	60	34.5	44.4
PG0426.151NL	0.15	2.0	2.2	57	26.0	40.0
PG0426.201NL	0.20	2.0	2.2	46	26.0	53.3
PG0426.221NL	0.22	2.0	2.2	40	26.0	58.6
PG0426.331NL	0.33	3.2	3.4	34	20.0	62.8
PG0426.471NL	0.47	3.2	3.4	26	20.0	89.4
PG0426.681NL	0.68	5.2	5.4	25	15.5	100.6
PG0426.821NL	0.82	7.8	8.0	24	13.0	99.3
PG0426.102NL	1.00	7.8	8.0	22	13.0	121.1
PG0426.152NL	1.50	11.5	11.8	18	9.0	153.6

Notes:

- 1. The temperature of the component (ambient plus temperature rise) must be within the specified operating temperature range.
- The saturation current, ISAT, is the current at which the component inductance drops by 30% (typical) at an ambient temperature of 25°C. This current is determined by placing the component in the specified ambient environment and applying a short duration pulse current (to eliminate self-heating effects) to the component.
- 3. The heating current, IDC, is the DC current required to raise the component temperature by approximately 40°C. The heating current is determined by mounting the component on a typical PCB and applying current for 30 minutes. The temperature is measured by placing the thermocouple on top of the unit under test. Take note that the component's performance varies depending on the system condition. It is suggested that the component be tested at the system level, to verify the temperature rise of the component during system operation.
- 4. Core loss approximation is based on published core data:

Core Loss = K1 * (f)^{1.33} * (K2 \triangle I)^{2.51} **Where: Core Loss** = in Watts

f = switching frequency in kHz

K1 & K2 = core loss factors

△I = delta I across the component in Ampere

K2△I = one half of the peak to peak flux density


across the component in Gauss


- 5. Unless otherwise specified, all testing is made at 100kHz, 0.1V_{AC}.
- Optional Tape & Reel packaging can be ordered by adding a "T" suffix to the part number (i.e. PG0426.101NL becomes PG0426.101NLT). Pulse complies to industry standard tape and reel specification EIA481.

PulseElectronics.com SPM2007_33 (01/24)



PG0426.XXXNL





For More Information:

Americas - prodinfo_power_americas@yageo.com | Europe - prodinfo_power_emea@yageo.com | Asia - prodinfo_power_asia@yageo.com

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2023. Pulse Electronics, Inc. All rights reserved.

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

