




■ Features

- High Current Capability
- Low Forward Voltage Drop

■ Mechanical Data

- package:SOD-123
- Polarity: Color band denotes cathode end
- Flammability rating of epoxy resin: UL 94V-0
- Mounting Position: Any.



■ Ordering Information

Part Number	Package	Marking	Packing	Quantity per reel	Reel Size
SD103AW	SOD-123	S4	Tape & Reel	3,000 PCS	7 inches
SD103BW	SOD-123	S5	Tape & Reel	3,000 PCS	7 inches
SD103CW	SOD-123	S6	Tape & Reel	3,000 PCS	7 inches

■ Maximum Ratings & Thermal Characteristics(Ratings at 25°C ambient temperature unless otherwise specified.)





Parameters	Symbol	SD103AW	SD103BW	SD103CW	Unit
Maximum repetitive peak reverse voltage	V _R RM	40	30	20	V
Maximum RMS voltage	V _R M _S	28	21	14	V
Maximum DC blocking voltage	V _D C	40	30	20	V
Maximum average forward rectified current	I _F M		350		mA
Peak forward surge current 8.3ms single half sine-wave	I _F SM		2		A
Power Dissipation	PD		400		mW
Typical thermal resistance	R _{θJA}		250		°C/W
Operating junction temperature	T _j		125		°C
Storage temperature range	T _{STG}		-50~+150		°C



■ Electrical Characteristics(Ratings at 25°C ambient temperature unless otherwise specified)


Parameters	Symbol	Test conditions	SD103AW	SD103BW	SD103CW	Unit
Maximum forward voltage	VF	IF = 20mA IF = 200mA		0.370 0.600		V
Maximum reverse breakdown voltage	VR	IR=100uA	40	30	20	V
Maximum reverse current	IR	VR=30V SD103AW VR=20V SD103BW VR=10V SD103CW		5.0		uA
Type junction capacitance	C _j	VR =0V, f = 1MHz		50		pF
Reverse recovery time	T _{rr}	IF=IR=200mA, I _{rr} =0.1xIR,RL=100 Ω		10		ns

■ Typical Characteristics





■ SOD-123 Package Outline Dimensions



Symbol	Dimensions	
	MIN	MAX
A	1.050	1.250
A1	0.000	0.100
A2	1.050	1.150
b	0.450	0.650
c	0.080	0.150
D	1.500	1.700
E	2.600	2.800
E1	3.550	3.850
L	0.500REF	
L1	0.250	0.450
θ	0°	8°