



MEAS | MEAS U5600, U5600

TE Internal #: 10202023-00

TE Internal Description: PRESS XDCC U5600-000005-100PA

0.1% Wireless Pressure Transducer

[View on TE.com >](#)

Sensors > Pressure Sensors > Pressure Transducers > 0.1% Wireless Pressure Transducer



Pressure Transducer Sensor Type: **Industrial Pressure Transducer, Wireless Pressure Transducer**

Pressure Range: **0 – 100 psi**

Pressure Type: **Absolute**

Pressure Transducer Supply Voltage: **2.7 V**

Output/Span: **Bluetooth**

[All 0.1% Wireless Pressure Transducer \(7\)](#)

## Features

### Product Type Features

Pressure Transducer Sensor Type	Industrial Pressure Transducer, Wireless Pressure Transducer
Pressure Type	Absolute

### Configuration Features

Electrical Connection	No Connector
Pressure Port/Fitting	1/4 MNPT

### Electrical Characteristics

Pressure Transducer Supply Voltage	2.7 V
------------------------------------	-------

### Dimensions

Dimensions	24 x 24 x 69 mm [.94 x .94 x 2.71 in]
------------	---------------------------------------

### Usage Conditions

Pressure	7 bar [15 psi]
Operating Temperature Range	-20 – 85 °C [-4 – 185 °F]

### Operation/Application

Proof Pressure Range	3X Rated
Pressure Range	0 – 100 psi



Output/Span	Bluetooth
Pressure Accuracy	±0.1% FSO

**Other**

Sensor Options	IP67 Protection
----------------	-----------------

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Compatible Parts**



Also in the Series | **MEAS U5600**



Pressure Transducers(7)

## Also in the Series | U5600



Pressure Transducers(7)

## Customers Also Bought



TE Part #2-320560-1  
TERMINAL,PIDG R 16-14 8, TAPE



TE Part #1SNG626092R0000  
EP-SGL-M32-GR-D



TE Part #91601-1  
CCII AMPMODU SHORT POINT REC  
24-20 ASSY




TE Part #2071509-1  
OJT-SS-124HM,00000



TE Part #DTM04-2P-EP10  
REC, 2P, BLK, 120 OHM RESISTOR,  
AU, B



TE Part #SM1-7  
STRING POT, 7.5 INCH RANGE



TE Part #1490413-1  
HYP10 SOLIS 8AWG NEST



TE Part #1490414-1  
HYP10 SOLIS 8AWG INDENTER



TE Part #843996-2  
TOOL, EXTRACTION RESET



## Documents

### CAD Files

#### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_10202023-00\\_C.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_10202023-00\\_C.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_10202023-00\\_C.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

#### U5600

English

### Product Specifications

#### Purchase Specification

English