

89-01KA-4R ✓ ACTIVE

MEAS | MEAS 89 Series

TE Internal #: 89-01KA-4R

TE Internal Description: 1000 PSIA 316L MV RIBBON PRESSURE SENSOR

9MM MV OUTPUT PRESSURE SENSOR

[View on TE.com >](#)



Sensors > Pressure Sensors > Media Isolated Pressure Sensors > 9MM MV OUTPUT PRESSURE SENSOR



Pressure: [ 1000 psi ]

Media Isolated Pressure Sensor Type: **Media Isolated mV Output Pressure Sensors**

Media Isolated Pressure Sensor Style: **Absolute**

Output/Span: **125 mV**

Operating Temperature Range: **-40 – 125 °C [ -40 – 257 °F ]**

[All 9MM MV OUTPUT PRESSURE SENSOR \(7\)](#)

## Features

### Product Type Features

Media Isolated Pressure Sensor Type	Media Isolated mV Output Pressure Sensors
Media Isolated Pressure Sensor Style	Absolute

### Configuration Features

Electrical Connection	Ribbon Cable
Pressure Port/Fitting	1/4-18 NPT (5/8 Hex)

### Electrical Characteristics

Supply Current	1.5 mA
----------------	--------

### Dimensions

Dimensions	Dia 9.04 x 13.2 mm [Dia .356 x .52 in]
------------	--

### Usage Conditions

Operating Temperature Range	-40 – 125 °C [ -40 – 257 °F ]
-----------------------------	-------------------------------

### Operation/Application

Proof Pressure Range	3X
	1000 psi
Output/Span	125 mV



## Packaging Features

Media Isolated Pressure Sensor Package

Threaded Process Fittings

## Other

Non-Linearity

± .25 %

## Product Compliance

For compliance documentation, visit the product page on [TE.com](https://www.te.com)>

EU RoHS Directive 2011/65/EU

Compliant

EU ELV Directive 2000/53/EC

Compliant

China RoHS 2 Directive MIIT Order No 32, 2016

No Restricted Materials Above Threshold

EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JUNE 2023 (235)

Candidate List Declared Against: JUNE 2023 (235)

SVHC &gt; Threshold:

Methanone, (diphenylphosphinyl)(2,4,6-trimethylphenyl)- (.11% in Component Part)

**Article Safe Usage Statements:**

Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content

Low Halogen - Br, Cl, F, I &lt; 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not reviewed for solder process capability


### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



### Also in the Series | MEAS 89 Series



### Customers Also Bought





## Documents

### CAD Files

Customer View Model

[ENG\\_CVM\\_CVM\\_89-01KA-4R\\_B1.3d\\_igs.zip](#)

English

### 3D PDF

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_89-01KA-4R\\_B1.3d\\_stp.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_89-01KA-4R\\_B1.2d\\_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[89C](#)

English