

85-015A-8R ✓ ACTIVE

MEAS | MEAS 85 Series

TE Internal #: 85-015A-8R

TE Internal Description: 15 PSIA 1/8 - 27 NPT PRESSURE SENSOR

13MM MV OUTPUT PRESSURE SENSOR

[View on TE.com >](#)



Sensors > Pressure Sensors > Media Isolated Pressure Sensors > 13MM MV OUTPUT PRESSURE SENSOR



Pressure: [ 15 psi ]

Media Isolated Pressure Sensor Type: **Media Isolated mV Output Pressure Sensors**

Media Isolated Pressure Sensor Style: **Absolute**

Output/Span: **100mV**

Operating Temperature Range: **-40 – 125 °C [ -40 – 257 °F ]**

[All 13MM MV OUTPUT PRESSURE SENSOR \(18\)](#)

## Features

### Product Type Features

Media Isolated Pressure Sensor Type	Media Isolated mV Output Pressure Sensors
Media Isolated Pressure Sensor Style	Absolute

### Configuration Features

Electrical Connection	Ribbon Cable
Pressure Port/Fitting	1/8-27 NPT

### Electrical Characteristics

Supply Current	1.5 mA
----------------	--------

### Dimensions

Dimensions	Dia 15.85 x 9.3 mm [Dia .624 x .366 in]
------------	---

### Usage Conditions

Operating Temperature Range	-40 – 125 °C [ -40 – 257 °F ]
-----------------------------	-------------------------------

### Operation/Application

Proof Pressure Range	3X
	15 psi
Output/Span	100mV

### Packaging Features



Media Isolated Pressure Sensor Package	Threaded Process Fittings, Weldable
--	-------------------------------------

**Other**

Non-Linearity	± .1 %
---------------	--------

**Product Compliance**

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

**Product Compliance Disclaimer**

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

**Compatible Parts**



## Also in the Series | MEAS 85 Series



Media Isolated Pressure Sensors(42)

## Customers Also Bought



TE Part #862382-1  
LGH RECPT HSG TYPE III



TE Part #154N-001G-R  
1 PSIG RIBBON CABLE MV PRESSURE SENSOR




TE Part #4525DO-SS3AS015APF  
PRESS XDCR,DIGITAL,PSI RANGE



TE Part #J05562074-000  
CORE 1J50 .108OD .625LG M2X0.4




TE Part #55778-1  
SOLIS 26-22 S-T HR R 8, AU




TE Part #73560087-000  
JL LVDT 100 MHR-4160




TE Part #20007909-00  
PRESS XDCR M5294-02001B-010BG



TE Part #10211257-00  
PRESS XDCR M5294-02001U-500BG



TE Part #10205351-00  
NTC TEMPERATURE SENSOR



TE Part #20013632-00  
PT9301-0400-212-1110: CTO-11500000-01

## Documents

[CAD Files](#)

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_85-015A-8R\\_G1.2d\\_dxf.zip](#)

[English](#)

[Customer View Model](#)



[ENG\\_CVM\\_CVM\\_85-015A-8R\\_G1.3d\\_igs.zip](#)

English

**Customer View Model**

[ENG\\_CVM\\_CVM\\_85-015A-8R\\_G1.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

---

**Datasheets & Catalog Pages**

**85C**

English