BUSSMANN SERIES

3-Pole, UL Type 1 DIN-Rail high SCCR surge protective devices







Catalog symbol:

- BSPMA3_WYGR
- BSPMA3_DLGR

Description:

The Bussmann™ series three-pole DIN-Rail UL® Listed open Type 1 surge protective devices feature a high 200 kA SCCR. Replaceable arrestor modules are mechanically coded with the base to ensure against installing an incorrect replacement. The unique module locking system fixes the module to the base, and allows it to be easily replaced without tools by simply depressing the release buttons.

Standard local visual status indication:

The module's visual indicator shows the protective status at a glance: green = good, red = replace.

Remote contact signaling:

The standard three-pole terminal remote Form C contact signaling relay has a floating changeover contact for use as a break or make contact, according to circuit concept.

Ratings:

- · System volts/types
 - 120/208 Vac 3-phase Wye
 - 277/480 Vac 3-phase Wye
 - 347/600 Vac 3-phase Wye
 - 240 Vac 3-phase Delta
 - 480 Vac 3-phase Delta
- · Short-circuit Current Rating (SCCR) 200 kA

Agency information:

- UL Listed open Type 1, ANSI/ UL 1449 4th Edition, Guide VZCA, VZCA7
- CSA® Type 4-1 Component Assembly, C22.2 No. 269.1-14, Class 2157-27
- · RoHS compliant


Mounting


· 35mm Din-Rail

Warranty

Five years

Dimensions - mm














| Specifications/ordering info | rmation | | | | |
|---|--|---------------------------------|---------------------------------|--------------------------------|---|
| System voltage/type | | 277/480 Vac 3-phase W/ve | 347/600 Vac 3-phase Wye | 240 Vac 3-phase Delta | 480 Vac 3-phase Delta |
| Catalog number | BSPMA3208WYGR | BSPMA3480WYGR | BSPMA3600WYGR | BSPMA3240DLGR | BSPMA3480DLGR |
| Replacement module | BPMA180UL (3) | BPMA385UL (3) | BPMA510UL (3) | BPMA275UL (3) | BPMA550UL (3) |
| catalog number (qty.) | BPIVIA 180UL (3) | BPIVIA385UL (3) | BPIVIA5 IUUL (3) | BPIVIAZ/5UL (3) | BPIVIA55UUL (3) |
| SPD class acc. to ANSI/UL | Open-Type 1 SPD | | | | |
| 1449 4th Ed. | Орен-туре т от в | | | | |
| SPD class acc. to CSA - C22.2 No. 269.1-14 | Type 4-1 Component Assembly | | | | |
| Nominal system voltage (U _N) | | | | | |
| [L-G] / [L-L] | 120 Vac / 208 Vac | 277 Vac / 480 Vac | 347 Vac / 600 Vac | 240 Vac / 240 Vac | 480 Vac / 480 Vac |
| Nominal power frequency | 50 / 60 Hz | | | | |
| Max. continuous operating | 1001/ 10001/ | | 540.1/ / 4000.1/ | | ===>/ / / / / / / / / / / / / / / / / / |
| voltage AC (MCOV) [L-G] / | 180 Vac / 360 Vac | 385 Vac / 770 Vac | 510 Vac / 1020 Vac | 275 Vac / 550 Vac | 550 Vac / 1100 Vac |
| [L-L] | | | | | |
| Nominal discharge current (L) (8x20µs) | 20 kA | | | | |
| Max. discharge current (I) | | | | | |
| (8/20) | 50 kA | | | | |
| Voltage Protection Rating | | | | | |
| (VPR) [L-G] / [L-L] | $600 V_{pk} / 1200 V_{pk}$ | $1200 V_{pk} / 2500 V_{pk}$ | $1500 V_{pk} / 3000 V_{pk}$ | $800 V_{pk} / 1500 V_{pk}$ | $1800 V_{pk} / 3000 V_{pk}$ |
| Short Circuit Current Rating | | | 000 4 | | |
| (SCCR) | 200 kA | | | | |
| Operating temperature | -31 to 185 (-35 to 85) | | | | |
| range (T _{II}) °F (°C) | -31 (0 100 (-30 (0 00) | | | | |
| Operating state / fault | Green = good ; Red = replace | | | | |
| indication | Green – good , ried – replace | | | | |
| Wire range (60/75°C Cu, | 4-14 AWG (2.5-25 mm²) | | | | |
| solid/stranded) | | | | | |
| Terminal torque | 35-45 (4-5.1) | | | | |
| Mounting | 35 mm DIN-Rail per EN 60715 | | | | |
| Enclosure material | Thermoplastic, UL 94 V0 | | | | |
| Protection | IP20 (finger-safe) | | | | |
| Capacity | 3 module(s), DIN 43880 UL Listed, Guide VZCA, VZCA7/CSA Component Acceptance Class 2157-27, RoHS | | | | |
| Agency information | | | | | 10.4.(200) |
| Weight - oz (g) | 10.93 (310) | 12.24 (347) | 13.05 (370) | 11.46 (325) | 13.4 (380) |
| Contact signaling | | Пал | ting (day) France C (CDDT) | | |
| Signaling type NEC Circuits | Floating (dry), Form C (SPDT) NEC Class 2 circuits only | | | | |
| Switching capacity AC (DC) | 250 V/5 A (250 V/0.1 A, 125 V/0.2 A, 75 V/0.5 A) | | | | |
| Wire range (60/75°C Cu, | | | | | |
| solid/stranded) | 16-22 AWG (1.5-0.34mm²) | | | | |
| Terminal torque - Ib-in (N•m) | 1.8 (0.2) | | | | |
| Tommiai torquo ib iii (IN-III) | | | 1.0 (0.2) | | |

Typical installation/system application:







The only controlled copy of this data sheet is the electronic read-only version located on the Eaton network drive. All other copies of this document are by definition uncontrolled. This bulletin is intended to clearly version located on the Later Herwork drive. All other copies of this ductarient are by definition uncontrolled. This bulletin is intended to clearly present comprehensive product data and provide technical information that will help the end user with design applications. Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin. Once a product has been selected, it should be tested by the user in all possible applications.

Eaton 1000 Eaton Boulevard Cleveland, OH 44122 Eaton.com

Bussmann Division 114 Old State Road Ellisville, MO 63021 United States Eaton.com/bussmannseries

© 2018 Eaton All Rights Reserved Printed in USA Publication No. 10773 — BU-MC18007 November 2018

Eaton, and Bussmann are valuable trademarks of Eaton in the U.S. and other countries. You are not permitted to use the Eaton trademarks without prior written consent of Eaton.

CSA is a registered trademark of the Canadian Standards Group. NEC is a registered trademark of the National Fire Protection Association, Inc. UL is a registered trademark of the Underwriters Laboratories, Inc.

For Eaton's Bussmann series product information, call 1-855-287-7626 or visit: Eaton.com/bussmannseries

Follow us on social media to get the latest product and support information.









