



ANATECH ELECTRONICS INC
RF & Microwave Filters & Products

2500-2520 MHz / 2670-2690 MHz Cavity Duplexer


Part Number: AD2510-2680D371



Characteristics	Band 1	Band 2
Passband:	2500-2520 MHz	2670-2690 MHz
Bandwidth:	20 MHz	20 MHz
Passband Return Loss:	>15 dB	>15 dB
Passband Insertion Loss:	< 1 dB	< 1 dB
Passband Ripple:	0.2 dB	0.2 dB
Input / Output Impedance:	50 Ohms	50 Ohms
Isolation:	> 70 dB	> 70 dB
Power Handling:	25 W Min	25 W Min

<u>Mechanical</u>	
Mounting Method:	Threaded Mounting Holes
Connector Type:	SMA (F)
Dimensions:	4.50 x 2.0 x 1.14 in
<u>Environmental</u>	
Operating Temperature:	-40 to +70 deg.C
Storage Temperature:	-50 to +90 deg.C
Shock:	20 G. 11ms
Vibration:	20 G. 5 to 200 Hz

Outline Drawing:



DS-D371-08202015-Rev0




ANATECH ELECTRONICS INC
RF & Microwave Filters & Products

2500-2520 MHz / 2670-2690 MHz Cavity Duplexer

Part Number: AD2510-2680D371



Response Plot:



DS-D371-08202015-Rev0