


Wire Range	Insulation Diameter	Reel Q'ty
AWG #22~#28	1.50 MAX. (.059)	10,000 PCS.


### Ordering Code

$\frac{CI31}{①}$ 
 $\frac{T02}{②}$ 
 $\frac{*}{③}$ 
 $\frac{*}{④}$ 
 $\frac{E}{⑤}$ 
 $\frac{0}{⑥}$

- ① Series No.
- ② Type: T02= AWG #22 ~ #28
- ③ Plating: 1= 1.52 $\mu$ m(60 $\mu$ " ) Min. Tin over 0.38 $\mu$ m(15 $\mu$ " ) Nickel  
 A= Selective Gold Flash Plated over 1.27 $\mu$ m(50 $\mu$ " )Nickel  
 B= Selective 0.38 $\mu$ m(15 $\mu$ " ) gold plated over 1.27 $\mu$ m(50 $\mu$ " ) Nickel
- ④ Material: B= Brass  
 P= Phosphor Bronze
- ⑤ Plating method: E= Pre-tinned
- ⑥ Option: 0= Standard




SEC: A-A



SEC: B-B

**RoHS Compliant**

SYMBOL	NAME	DATE	REVISIONS	APPROVED BY:	DATE	UNIT:	TITLE:	 瀚荃股份有限公司 CviLux Corporation	
⑤	Karen	4/07-20	ECNT120089/ECRB120007			mm / inch	2.54MM(.100") CRIMP TERMINAL		
④	Erin	5/7-12	ECR12021-0/ECN12074-0	DRAWN BY: Karen	4/13-20	TOLERANCE UNLESS OTHERWISE SPECIFIED .X ± 0.20/.008    .X' ± 1" .XX ± 0.10/.004    .X" ± .XXX ± 0.05/.002    .XX" ±	MATERIAL:		
③	Una	04/20-11	ECN11074	ENGINEER: Sun	4/13-20				
②	EDDY	10/23/03	ECN03367, ECR03013-1	CHECKED BY: Eisley	4/13-20				
①				APPROVED BY: Eisley	4/13-20	FINISH:	DRAWING NO. CI3105SK	PART NO. CI31T02**E0	
								SCALE 5 / 1	SHEET 1 OF 1

**CVILUX**  
 2020.04.16  
**ISSUED**