


## POM-3042L-R Omni-Directional Microphone



3541 Stop Eight Road • Dayton, Ohio 45414

## **Product Overview**


- 6mm overall diameter and 3mm height with solder pads
- -42 dB sensitivity for picking up low level sound
- Wide 2 to 10 VDC operating voltage and 50-16,000 Hz frequency response
- >68 dB signal-to-noise ratio and 2.2 kOhm impedance
- Omni-directional polar pattern for great off-axis response













## POM-3042L-R Omni-Directional Microphone

Mechanical and Environment Testing					
Test Description	Test Condition				
High Temperature	70°C with random humidity for 200 hours				
Low Temperature	-25°C with random humidity for 200 hours				
Humidity	40°C with 90% relative humidity for 200 hours				
Vibration	3 mm movement for 3 minutes in each of 3 axis				
Drop Test	70 cm free fall onto 20 mm thick board, two directions				
Temperature Cycle Test	-10°C to 50°C, 5 cycles				








SPECIFICATIONS							
PARAMETERS	VALUES	UNIT					
DIRECTIVITY	OMINI	-					
SENSITIVTY	-42 ± 3	dB					
STANDARD OPERATING VOLTAGE	2	Vdc					
MAX OPERATING VOLTAGE	10	Vdc					
CURRENT CONSUMPTION (MAX)	0.5	mA					
IMPEDANCE	2.2	KOhm					
SIGNAL TO NOISE RATIO (MIN.)	60	dB					
TERMINAL	SOLDER PADS	-					
INTERNAL CAPACITOR	N/A	pF					

THIS DOCUMENT CONTAINS DATA PROPRIETARY TO PROJECTS UNLIMITED, INC. ANY USE OR REPRODUCTION, IN ANY FORM, WITHOUT PRIOR WRITTEN PERMISSION OF PROJECTS UNLIMITED, INC. IS PROHIBITED. ©2003, Projects Unlimited Inc.

REVISION HISTORY						
LTR	DESCRIPTION	DATE	APPROVED			
-	RELEASED FROM ENGINEERING	1/27/2006				
Α	REVISED TO INVENTOR 3-D DRAWING TEMPLATE	10/7/2010	B.R.			







## NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. SPECIFICATIONS SUBJECT TO CHANGE OR WITHDRAWL WITHOUT NOTICE.
- 3. THIS PART IS RoHS 2002/95/EC COMPLIANT.

UNLESS OTHERWISE		Designed by	Date	Checked by	Date	Approved by	Date	D	rawn Date	
SPECIFIED: DIMENSIONS ARE IN	SIZE	J.A.F.	1/27/2006	E.P.	1/27/2006	B.R.	1/27/20	06 10	0/7/2010	
MILLIMETERS,  TOLERANCES ARE ±0.5 AND	Α3	pul.			POM-3042L-R					
ANGLES ARE ±3°.	$\Lambda$ 0		או ולוכ	тм	Micro	ahana		Edition	Sheet	
POM-3042L-R.idw			a projects unlimited co	INC Impany	Micro	Jilone		-	1/1	

Drawn Date