




Connectors > Contacts > Connector Contacts



Contact Type: **Receptacle**

Contact Mating Area Plating Material: **Tin**

Wire Contact Termination Area Plating Material: **Tin**

Operating Voltage: **250 VDC**

Features

Product Type Features

Discrete Wire Type	Stranded
Sealable	No

Electrical Characteristics

Operating Voltage	250 VDC
-------------------	---------

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
Wire Contact Termination Area Plating Thickness	1.27 – 2.54 μm[50 – 100 μin]
Wire Contact Termination Area Plating Material Finish	Bright
Contact Mating Area Plating Material Thickness	1.27 – 2.54 μm[50 – 100 μin]
Contact Mating Area Plating Material Finish	Bright
Contact Orientation	Straight
Barrel Type	Open
Contact Type	Receptacle
Contact Mating Area Plating Material	Tin
Wire Contact Termination Area Plating Material	Tin



Contact Retention Within Housing	With
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	5 A

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	With
Contact Retention Type Within Housing	Locking Lance

Dimensions

Compatible Insulation Diameter Range	1.5 – 2.79 mm [.059 – .109 in]
Wire Size	1624 – 6529 CMA

Usage Conditions

Operating Temperature Range	-40 – 105 °C [-40 – 221 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Packaging Features

Packaging Quantity	6000
Packaging Method	Reel

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2266495-1
OCEAN-2.0-APPLICATOR-S-062F1100



TE Part # 2266495-2
OCEAN-2.0-APPLICATOR-S-062F1100A



TE Part # 7-2266495-1
OCEAN-2.0-APPLICATOR-S-062F1100




TE Part # 7-2266495-2
OCEAN-2.0-APPLICATOR-S-062F1100A




KIT
REPRESENTATION ONLY

TE Part # 7-2266495-7
OCEAN_2.0_SPARE_PART_KIT-062F1100

Also in the Series | Micro MATE-N-LOK



Connector Contacts(27)



Insertion & Extraction Tools(1)




Rectangular Power Connectors(469)

Customers Also Bought



TE Part #1775441-2
EMIX CONN., 1.5MM PITCH, RCPT,
HSG, 2P



TE Part #1775442-1
EMIX CONN., 1.5mm PITCH, TERMI



TE Part #60772-2
RING CRIMP 18-14 AWG TPBR



TE Part #2008570-4
4 POS MICRO MNL, SIDE LATCH, B



TE Part #2238173-3
250 FASTON,REC.,22-12 AWG,TPBR



TE Part #2176308-5
RP 1E 0.1W 147K 0.1% 25PPM 5K RL



TE Part #1-2176308-3
RP 1E 0.1W 178K 0.1% 25PPM 5K RL



TE Part #2-2176308-1
RP 1E 0.1W 215K 0.1% 25PPM 5K RL



TE Part #2-320093-1
TERMINAL,SOLIS R 16-14 10

Documents

Product Drawings

[Socket Micro MNL, TIN 22-18 AW](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_2008625-1_A.2d_dxf.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_2008625-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2008625-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



MICRO MATE-N-LOK CONNECTOR SYSTEM

English

Product Specifications

Application Specification

English