


EPC2204 – Enhancement Mode Power Transistor


 $V_{DS}, 100\text{ V}$
 $R_{DS(on)}, 6\text{ m}\Omega$
 $I_D, 29\text{ A}$


Gallium Nitride's exceptionally high electron mobility and low temperature coefficient allows very low $R_{DS(on)}$ while its lateral device structure and majority carrier diode provide exceptionally low Q_G and zero Q_{RR} . The end result is a device that can handle tasks where very high switching frequency, and low on-time are beneficial as well as those where on-state losses dominate.

Application Notes:

- Easy-to-use and reliable gate, Gate Drive ON = 5 V typical, OFF = 0 V (negative voltage not needed)
- Top of FET is electrically connected to source

Questions:



Die Size: 2.5 x 1.5 mm

EPC2204 eGaN® FETs are supplied only in passivated die form with solder bars.

Applications

- DC-DC Converters
- Isolated DC-DC Converters
- Lidar
- Sync rectification for AC-DC and DC-DC
- Point of Load Converters
- USB-C
- Class-D Audio
- LED Lighting
- eMobility

Benefits

- Ultra High Efficiency
- No Reverse Recovery
- Ultra Low Q_G
- Small Footprint

Scan QR code or click link below for more information including reliability reports, device models, demo boards!



<https://l.ead.me/EPC2204>

Maximum Ratings

PARAMETER		VALUE	UNIT
V_{DS}	Drain-to-Source Voltage (Continuous)	100	V
	Drain-to-Source Voltage (up to 10,000 5 ms pulses at 150 °C)	120	
I_D	Continuous ($T_A = 25^\circ\text{C}$)	29	A
	Pulsed (25°C , $T_{PULSE} = 300\ \mu\text{s}$)	125	
V_{GS}	Gate-to-Source Voltage	6	V
	Gate-to-Source Voltage	-4	
T_J	Operating Temperature	-40 to 150	°C
T_{STG}	Storage Temperature	-40 to 150	

Thermal Characteristics

PARAMETER		TYP	UNIT
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	1	°C/W
$R_{\theta JB}$	Thermal Resistance, Junction-to-Board	2.5	
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient (Note 1)	64	

Note 1: $R_{\theta JA}$ is determined with the device mounted on one square inch of copper pad, single layer 2 oz copper on FR4 board. See https://epc-co.com/epc/documents/product-training/Appnote_Thermal_Performance_of_eGaN_FETs.pdf for details.

Static Characteristics ($T_J = 25^\circ\text{C}$ unless otherwise stated)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
BV_{DSS}	Drain-to-Source Voltage	$V_{GS} = 0\text{ V}$, $I_D = 0.25\text{ mA}$	100			V
I_{DSS}	Drain-Source Leakage	$V_{GS} = 0\text{ V}$, $V_{DS} = 80\text{ V}$		0.04	0.2	mA
I_{GSS}	Gate-to-Source Forward Leakage	$V_{GS} = 5\text{ V}$		0.01	1.3	
	Gate-to-Source Forward Leakage [#]	$V_{GS} = 5\text{ V}$, $T_J = 125^\circ\text{C}$		0.3	6.7	
	Gate-to-Source Reverse Leakage	$V_{GS} = -4\text{ V}$		0.03	0.2	
$V_{GS(TH)}$	Gate Threshold Voltage	$V_{DS} = V_{GS}$, $I_D = 4\text{ mA}$	0.8	1.1	2.5	V
$R_{DS(on)}$	Drain-Source On Resistance	$V_{GS} = 5\text{ V}$, $I_D = 16\text{ A}$		4.4	6	m Ω
V_{SD}	Source-Drain Forward Voltage [#]	$I_S = 0.5\text{ A}$, $V_{GS} = 0\text{ V}$		1.6		V

[#] Defined by design. Not subject to production test.

Dynamic Characteristics# ($T_j = 25^\circ\text{C}$ unless otherwise stated)

PARAMETER		TEST CONDITIONS	MIN	TYP	MAX	UNIT
C_{ISS}	Input Capacitance	$V_{DS} = 50\text{ V}, V_{GS} = 0\text{ V}$		644	851	pF
C_{RSS}	Reverse Transfer Capacitance			2.3		
C_{OSS}	Output Capacitance			304	456	
$C_{OSS(ER)}$	Effective Output Capacitance, Energy Related (Note 2)	$V_{DS} = 0\text{ to }50\text{ V}, V_{GS} = 0\text{ V}$		401		
$C_{OSS(TR)}$	Effective Output Capacitance, Time Related (Note 3)			501		
R_G	Gate Resistance			0.4		Ω
Q_G	Total Gate Charge	$V_{DS} = 50\text{ V}, V_{GS} = 5\text{ V}, I_D = 16\text{ A}$		5.7	7.4	nC
Q_{GS}	Gate-to-Source Charge	$V_{DS} = 50\text{ V}, I_D = 16\text{ A}$		1.8		
Q_{GD}	Gate-to-Drain Charge			0.8		
$Q_{G(TH)}$	Gate Charge at Threshold			1		
Q_{OSS}	Output Charge	$V_{DS} = 50\text{ V}, V_{GS} = 0\text{ V}$		25	38	
Q_{RR}	Source-Drain Recovery Charge			0		

Defined by design. Not subject to production test.

All measurements were done with substrate connected to source.

Note 2: $C_{OSS(ER)}$ is a fixed capacitance that gives the same stored energy as C_{OSS} while V_{DS} is rising from 0 to 50% BV_{DSS} .

Note 3: $C_{OSS(TR)}$ is a fixed capacitance that gives the same charging time as C_{OSS} while V_{DS} is rising from 0 to 50% BV_{DSS} .

Figure 1: Typical Output Characteristics at 25°C




Figure 2: Typical Transfer Characteristics




Figure 3: $R_{DS(on)}$ vs. V_{GS} for Various Drain Currents




Figure 4: Typical $R_{DS(on)}$ vs. V_{GS} for Various Temperatures




Figure 5a: Typical Capacitance (Linear Scale)




Figure 5b: Typical Capacitance (Log Scale)




Figure 6: Typical Output Charge and C_OSS Stored Energy




Figure 7: Typical Gate Charge




Figure 8: Reverse Drain-Source Characteristics





Figure 9: Normalized On-State Resistance vs. Temperature



Note: Negative gate drive voltage increases the reverse drain-source voltage. EPC recommends 0V for OFF.

Figure 10: Normalized Threshold Voltage vs. Temperature




Figure 11: Safe Operating Area








Figure 12: Transient Thermal Response Curves




TAPE AND REEL CONFIGURATION

4 mm pitch, 8 mm wide tape on 7" reel



Loaded Tape Feed Direction →




Die is placed into pocket solder bar side down (face side down)

EPC2204 (Note 1)	Dimension (mm)		
	Target	MIN	MAX
a	8.00	7.90	8.30
b	1.75	1.65	1.85
c (Note 2)	3.50	3.45	3.55
d	4.00	3.90	4.10
e	4.00	3.90	4.10
f (Note 2)	2.00	1.95	2.05
g	1.50	1.50	1.60
h	0.50	0.45	0.55

Note 1: MSL 1 (moisture sensitivity level 1) classified according to IPC/JEDEC industry standard.

Note 2: Pocket position is relative to the sprocket hole measured as true position of the pocket, not the pocket hole.


DIE MARKINGS



Part Number	Laser Markings		
	Part # Marking Line 1	Lot_Date Code Marking Line 2	Lot_Date Code Marking Line 3
EPC2204	2204	YYYY	ZZZZ


DIE OUTLINE

Solder Bump View



DIM	Micrometers		
	MIN	Nominal	MAX
A	2470	2500	2530
B	1470	1500	1530
c	1155	1175	1195
d	1330	1350	1370
e		500	
f	230	250	270
g	280	300	320
h	805	825	845
j		787.5	
k		225	
m		250	


Side View



Pad 1 is Gate;
 Pads 2, 4, 6 are Source;
 Pads 3, 5 are Drain

Note: Dimensions d and c are centered

RECOMMENDED LAND PATTERN
(units in μm)




Land pattern is solder mask defined

DIM	Nominal
A	2500
B	1500
c1	1155
d1	1330
e	500
f1	230
g1	280
h1	805
j	787.5
k	225
m	250

Pad 1 is Gate;
Pads 2, 4, 6 are Source;
Pads 3, 5 are Drain

RECOMMENDED STENCIL DRAWING
(units in μm)



DIM	Nominal
A	2500
B	1500
c1	1155
d1	1330
e	500
f1	230
f2	210
g1	280
h1	805
j	787.5
k	225
m	250

Recommended stencil should be 4 mil (100 μm) thick, must be laser cut, openings per drawing.

The corner has a radius of R60.

Intended for use with SAC305 Type 4 solder, reference 88.5% metals content.

Split stencil design can be provided upon request, but EPC has tested this stencil design and not found any scooping issues.

Additional assembly resources available at <https://epc-co.com/epc/DesignSupport/AssemblyBasics.aspx>

Efficient Power Conversion Corporation (EPC) reserves the right to make changes without further notice to any products herein to improve reliability, function or design. EPC does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights, nor the rights of others.

eGaN® is a registered trademark of Efficient Power Conversion Corporation.
EPC Patent Listing: epc-co.com/epc/AboutEPC/Patents.aspx

Information subject to change without notice.
Revised December, 2022