

August 1991

Features



- 12A, 180V and 200V
- $r_{DS(on)} = 0.25\Omega$
- SOA is Power-Dissipation Limited
- Nanosecond Switching Speeds
- Linear Transfer Characteristics
- High Input Impedance
- Majority Carrier Device

Description

The RFM12N18 and RFM12N20 and the RFP12N18 and RFP12N20 are n-channel enhancement-mode silicon-gate power field-effect transistors designed for applications such as switching regulators, switching converters, motor drivers, relay drivers, and drivers for high-power bipolar switching transistors requiring high speed and low gate-drive power. These types can be operated directly from integrated circuits.


The RFM-types are supplied in the JEDEC TO-204AA steel package and the RFP-series types in the JEDEC TO-220AB plastic package.

Packages



Terminal Diagram

N-CHANNEL ENHANCEMENT MODE



4

N-CHANNEL
POWER MOSFETs

Absolute Maximum Ratings ($T_C = 25^\circ C$), Unless Otherwise Specified

	RFM12N18	RFM12N20	RFP12N18	RFP12N20	UNITS
Drain-Source Voltage	V_{DSS}	180	200	180	V
Drain-Gate Voltage ($R_{GS} = 1m\Omega$)	V_{DGR}	180	200	180	V
Continuous Drain Current					
RMS Continuous	I_D	12	12	12	A
Pulsed Drain Current	I_{DM}	30	30	30	A
Gate-Source Voltage	V_{GS}	± 20	± 20	± 20	V
Maximum Power Dissipation					
$T_C = +25^\circ C$	P_D	100	100	75	W
Above $T_C = +25^\circ C$, Derate Linearly		0.8	0.8	0.6	$W/^\circ C$
Operating and Storage Junction	T_J, T_{STG}	-55 to +150	-55 to +150	-55 to +150	$^\circ C$
Temperature Range					

RFM12N18, RFM12N20, RFP12N18, RFP12N20




Fig. 1 - Maximum safe operating areas for all types.




Fig. 2 - Power dissipation vs. case temperature derating curve for all types.




Fig. 3 - Typical normalized gate threshold voltage as a function of junction temperature for all types.




Fig. 4 - Normalized drain-to-source on resistance as a function of junction temperature for all types.




Fig. 5 - Typical transfer characteristics for all types.

RFM12N18, RFM12N20, RFP12N18, RFP12N20

