


TE Internal #: 3-1823449-1 Housing for Male Terminals, Wire-to-Wire, 22 Position, .157 in / .236 in [4 mm / 6 mm] Centerline, Sealable, Black, Signal, Panel Mount View on TE.com >



Connectors > Automotive Connectors > Automotive Housings



Connector System: Wire-to-Wire

Number of Positions: 22

Connector & Housing Type: Housing for Male Terminals

Centerline (Pitch): 4 mm, 6 mm [.157 in, .236 in]

Sealable: Yes

Features

Product Type Features

Mixed & Hybrid Connector	Yes
Connector Shape	Rectangular
Connector System	Wire-to-Wire
Connector & Housing Type	Housing for Male Terminals
Sealable	Yes
Primary Locking Feature	On the Terminal
Configuration Features	
Number of Positions	22
Number of Rows	3, 4
Electrical Characteristics	
Operating Voltage	42 VAC
Nominal Voltage Architecture	12 V, 24 V, 42 V
Body Features	
Cable Exit Angle	180°
Primary Product Color	Black

3-1823449-1

Housing for Male Terminals, Wire-to-Wire, 22 Position, .157 in / .236 in [4 mm / 6 mm] Centerline, Sealable, Black, Signal, Panel Mount



Connector & Keying Code	С
Contact Features	
Contact Size	1.6mm, 2.8mm
Contact Type	Tab
Mating Tab Width	1.6 mm, 2.8 mm[.063 in][.11 in]
Mechanical Attachment	
Terminal Position Assurance	Yes
Strain Relief	Without
Mating Alignment Type	Keyed
Mating Alignment	With
Connector Mounting Type	Panel Mount
Housing Features	
Housing Material	PBT GF
Centerline (Pitch)	4 mm, 6 mm[.157 in][.236 in]
Dimensions	
Connector Height	49 mm[1.94 in]
Product Width	32.4 mm[1.27 in]
Product Length	48.4 mm[1.9 in]
Row-to-Row Spacing	6 mm[.236 in]
Usage Conditions	
Operating Temperature (Max)	70 °C, 75 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C[158 °F][167 °F][176 °F][185 °F [194 °F][212 °F][221 °F][230 °F]
Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
Operation/Application	
Circuit Application	Signal
Industry Standards	
Degree of Protection	IP67, IP69K
UL Flammability Rating	UL 94V-0
Packaging Features	
Packaging Quantity	285
Packaging Method	Box

3-1823449-1

Housing for Male Terminals, Wire-to-Wire, 22 Position, .157 in / .236 in [4 mm / 6 mm] Centerline, Sealable, Black, Signal, Panel Mount



Other

Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts



Customers Also Bought

3-1823449-1

Housing for Male Terminals, Wire-to-Wire, 22 Position, .157 in / .236 in [4 mm / 6 mm] Centerline, Sealable, Black, Signal, Panel Mount





Documents

Product Drawings 22POS, MIXED, TAB HSG, ASSY

English

CAD Files 3D PDF

3D

Customer View Model ENG_CVM_CVM_3-1823449-1_A.2d_dxf.zip

English

Customer View Model

```
ENG_CVM_CVM_3-1823449-1_A.3d_igs.zip
```

English

Customer View Model

```
ENG_CVM_CVM_3-1823449-1_A.3d_stp.zip
```

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications Application Specification

German