## 3SU1130-7AA10-1NA0-Z Y15

## **Data sheet**



Coordinate switch, 22 mm, round, plastic with metal front ring, black, 2 switch positions, horizontal latching, without mechanical interlocking, in O position, with holder, 1 NO, 1 NO, screw terminal, with laser labeling, upper case and lower case, always upper case at the beginning of the word

product brand name	SIRIUS ACT
product designation	Coordinate switches
design of the product	Complete unit
product type designation	3SU1
product line	Plastic with metal front ring, matt, 22 mm
manufacturer's article number	
<ul> <li>of supplied contact module at position 1</li> </ul>	3SU1400-1AA10-1BA0
<ul> <li>of supplied contact module at position 3</li> </ul>	3SU1400-1AA10-1BA0
<ul> <li>of the supplied holder</li> </ul>	3SU1550-0BA10-0AA0
<ul> <li>of the supplied actuator</li> </ul>	3SU1030-7AA10-0AA0
Enclosure	
shape of the enclosure front	round
Actuator	
design of the actuating element	without mechanical interlock
principle of operation of the actuating element	latching
direction of actuation	horizontal
product extension optional light source	No
color of the actuating element	black
material of the actuating element	plastic
shape of the actuating element	Extended handle
outer diameter of the actuating element	30.5 mm
marking of the actuating element	Any inscription, text in upper/lower case, all words begin with upper case letters
number of contact modules	2
number of switching positions	2
Maximum deflection angle [°]	30°
Front ring	
product component front ring	Yes
design of the front ring	high
material of the front ring	Metal, matt
color of the front ring	sand gray
Holder	
material of the holder	Plastic
General technical data	
product function positive opening	No
insulation voltage rated value	500 V
degree of pollution	3
type of voltage of the operating voltage	AC/DC
surge voltage resistance rated value	6 kV

protection class IP	IP65, IP67
of the terminal	IP20
shock resistance	
according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
vibration resistance	
according to IEC 60068-2-6	10 500 Hz: 5g
operating frequency maximum	2 400 1/h
mechanical service life (switching cycles)	
as operating period per direction of actuation typical	100 000
electrical endurance (switching cycles) typical	10 000 000
electrical endurance (switching cycles) with	10 000 000
contactors 3RT1015 to 3RT1026 typical	
thermal current	10 A
reference code according to IEC 81346-2	S
continuous current of the C characteristic MCB	10 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A
continuous current of the DIAZED fuse link gG	10 A
Substance Prohibitance (Date)	10/01/2014
operating voltage	
• at AC	
— at 50 Hz rated value	5 500 V
— at 60 Hz rated value	5 500 V
at DC rated value	5 500 V
Power Electronics	
contact reliability	One maloperation per 100 million (17 V, 5 mA), one maloperation per 10
<u> </u>	million (5 V, 1 mA)
Auxiliary circuit	
design of the contact of auxiliary contacts	Silver alloy
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	2
Connections/ Terminals	
type of electrical connection of modules and accessories	Screw-type terminal
type of connectable conductor cross-sections	
solid with core end processing	2x (0.5 0.75 mm²)
solid without core end processing     solid without core end processing	2x (1.0 1.5 mm²)
finely stranded with core end processing	2x (0.5 1.5 mm²)
finely stranded with core end processing     finely stranded without core end processing	2x (1.0 1.5 mm²)
at AWG cables	2x (1,0 1,3 mm ) 2x (18 14)
tightening torque of the screws in the bracket	1 1.2 N·m
tightening torque for auxiliary contacts with screw-type	0.8 1 N·m
terminals	5.5 T TT III
Safety related data	
B10 value with high demand rate according to SN 31920	100 000
proportion of dangerous failures	
with low demand rate according to SN 31920	20 %
with low demand rate according to SN 31920     with high demand rate according to SN 31920	20 %
failure rate [FIT] with low demand rate according to SN	100 FIT
31920	100111
Ambient conditions	
ambient temperature	
during operation	-25 +70 °C
during operation     during storage	-25 +70 °C
environmental category during operation according to IEC	3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 95%, no
environmental category during operation according to IEC 60721	condensation in operation permitted for all devices behind front panel)
Installation/ mounting/ dimensions	
fastening method	front plate mounting
of modules and accessories	Front plate mounting
height	40 mm
width	40 mm
shape of the installation opening	round
anape of the matanation opening	Tourid

22.3 mm	
0.4 mm	
71.3 mm	
30.5 mm	
53.7 mm	
Certificates/ approvals	

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1130-7AA10-1NA0-Z Y15

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1130-7AA10-1NA0-Z Y15

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SU1130-7AA10-1NA0-Z Y15

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) <a href="http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3SU1130-7AA10-1NA0-Z Y15&lang=en">http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3SU1130-7AA10-1NA0-Z Y15&lang=en</a>

last modified: 1/27/2022 🖸