

#### APRA2504F00Z

Request Samples



Check Inventory (>)



25.1 x 25.1 x 4.0 mm RoHS/RoHS II Compliant MSL Level = 1

### **Features**

- Complies with Automotive Qualification (AEC-Q200)
- Complies with IATF 16949 Certification
- Multiband GPS + Iridium patch
- Low VSWR  $\leq 3$
- RHCP polarization
- Peak Gain of 3.0 dBi
  - GPS: 2.0 dBiIridium: 3.0 dBi

### **Applications**

- Automotive
- GPS/Iridium applications
- IoT & M2M
- Industrial IoT
- Consumer electronics
- Wireless modules
- Video and surveillance
- Broadband cellular connectivity
- Networking & Telecommunications

#### **Product Image**







### APRA2504F00Z

Request Samples (>)



Check Inventory (>)



25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

### **Electrical Specifications**

Parameter	Specifi	Unit	
Operating Band	GPS Iridium		
Operating Frequency	$1575.42 \pm 1.023$	1610 ~ 1625	MHz
Center Frequency	1595	MITIZ	
Max VSWR	3		
Gain	2.0	3.0	dBi
Impedance	50	Ω	
Polarization	RH		

#### Note:

- Ground Plane size: 70 x 70 mm
- Actual electrical characteristics will depend on the size of ground plane in use.

### **Mechanical Specifications**

Parameter	Specification		
Antenna Dimension	25.1 x 25.1 x 4.0 mm		
Material	Ceramic		
Termination	Silver		
Mounting Type	Through-Hole + Adhesive Tape		

### **Environmental Specifications**

Parameter	Specification		
Operating Temperature	-40°C to +105°C		
Storage Temperature	-40 C to +103 C		
Frequency Temperature Coefficient (T <sub>f</sub> )	$-40^{\circ}$ C to $+105^{\circ}$ C $(0 \pm 20 \text{ ppm/ }^{\circ}$ C )		
RoHS / RoHS II Compliant	Yes		
MSL	1		
Environmentally Friendly	Pb free		
Relative Humidity	0~95%		
Soldering Feed Pin Temperature	+290 °C (3 seconds max)		





### APRA2504F00Z

Request Samples (>)




Check Inventory (>)



25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

#### **Product Dimension**



Unit: mm

### **Product Marking**







### APRA2504F00Z





Check Inventory (>)



25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1


### **Layout Dimensions**



TDL:±0,20

Unit: mm

### **Tape Dimensions**



Double – coated thin adhesive tape | Thickness: 0.12 mm

Unit: mm





### APRA2504F00Z

Request Samples (>)




Check Inventory (>)




25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

### VNA Test Measurement - Set up




### Radiation Measurement - Set up

XZ-Plane



YZ-Plane₽







APRA2504F00Z

Request Samples (>)




Check Inventory (>)



25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

### Test Measurement - Return Loss







### APRA2504F00Z

Request Samples




Check Inventory (>)



25.1 x 25.1 x 4.0 mm RoHS/RoHS II Compliant MSL Level = 1

#### Test Measurement - VSWR







#### APRA2504F00Z

Request Samples (>)




Check Inventory (>)



25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

### **Test Measurement – Smith Chart**







APRA2504F00Z

Request Samples (>)




Check Inventory (>)



25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

#### Radiation Measurement - 2D Pattern

### **XZ + YZ Plane : 1575.42 MHz**







APRA2504F00Z

Request Samples (>)




Check Inventory (>)



25.1 x 25.1 x 4.0 mm RoHS/RoHS II Compliant MSL Level = 1

### **XZ + YZ - Plane : 1621 MHz**



Pat	tern	Model No.	Test Mode	Freq(MHz)	Max Gain(dBi)	Min Gain(dBi)	Avg. Gain(dBi)	Source Polar.
1		APRA2504F00Z	XZ	1621.00	4.48 / 359.00	-7.91 / 122.00	-0.38	V+H
2		APRA2504F00Z	YZ	1621.00	4.32 / 359.00	-8.01 / 116.00	-0.36	V+H





#### APRA2504F00Z

Request Samples



Check Inventory (>)



25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

### **Soldering Condition**

Soldering should be done in 3 seconds by a feed pin of maximum temperature +290 °C.

#### **Precautions**

- Do not direct solder onto the silver electrode of the antenna pattern.
- Do not use the patch antenna in a corrosive gaseous atmosphere for example sulfur gas, chlorine gas.





#### APRA2504F00Z

Request Samples



Check Inventory (>)




25.1 x 25.1 x 4.0 mm RoHS/RoHS II Compliant MSL Level = 1

#### **Packaging Information**

Dimensions of the inner carton: 261 x 152 x 118 mm Dimensions of the outer Carton: 330 x 280 x 254 mm

Number of pcs per outer Carton: 800



ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

