

Gemini

Part No: LMA101.A.BI.001

Description:

Gemini 2*5G/4G MIMO Magnetic/Desk/Wall Mount Antenna

Features:

5G/4G MIMO Antenna

Covers Cellular Bands between 600-6000MHz

High Efficiency Antenna

IP67 Rating

- 3 Way Mounting Options
- Magnetic Mount
- Wall Mount
- Desktop Mount

2*Low Loss 1m CFD-200 Cables, SMA(M)

Cable and Connector Customizable

Enclosure Dimensions: 164*164*36.5mm

RoHS & Reach Compliant

www.taoglas.com



1.	Introduction	3
2.	Specifications	4
3.	Active Antenna Characteristics	8
4.	4G Antenna Characteristics	13
5.	Radiation Patterns	16
6.	Mechanical Drawing	33
7.	Packaging	34
8.	Application Note	35
	Changelog	38

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.





1. Introduction



Taoglas Gemini LMA101 is a 2* 5G/4G MIMO Antenna for use with all 5G/4G cellular routers and access points worldwide requiring MIMO connectivity. It includes two high-efficiency 5G/4G antennas that operate at all common and 5G/4G bands worldwide from 600MHz to 6000MHz. It has been designed to include 3G and 2G bands, meaning the antenna can also be used for fallback in circumstances where 5G/4G is not available. High isolation and low ECC between the two embedded MIMO antennas prevent self-interference and the low loss CFD-200 cables are used to keep efficiency high over longer cable lengths of up to 5 meters.

This unique antenna offers three mounting options for easy installation. The base features eight supermagnets for easy and secure installation on metal surfaces. The rear of the enclosure features a bracket to enables wall installation, keeping your workstation free from clutter or the antenna can also be placed directly on a flat surface using the stand. The LMA101 can be used both indoors and outdoors as the robust external enclosure is fully IP67 rated.

Typical Applications include:

- HD Real-time Streaming Video over LTE
- Intelligent Transport Systems
- Digital Signage and HD Broadcast Systems
- Wireless 5G/4G MIMO M2M devices with legacy 3G/2G functionality.

Cable length and connector types are customizable. Contact your regional Taoglas sales office for support.



2.

Specifications

Electrical									
Band	Frequency (MHz)		Efficiency (%)	Average Gain (dB)	Peak Gain (dBi)	Impedance	Max Input Power	Polarization	Radiation Pattern
5GNR/4G	617~698	MIMO 1	40	-4.9	-0.3				
Band 71	017 098	MIMO 2	39.9	-4.7	-0.2				
4G/3G	698~806	MIMO 1	60.9	-2.2	2.1				
Band 12,13,14,17,28,29	098 800	MIMO 2	64	-2	2.3				
4G/3G/NB-IoT/Cat M	824~960	MIMO 1	34.5	-4.7	-0.2				
Band 5,8,18,19,20,26,27	824 960	MIMO 2	43	-3.7	0.7				
5GNR/4G	1427~1510	MIMO 1	35.1	-4.5	1.7				
Band 21,32,74,75,76	1427~1518	MIMO 2	25.7	-5.8	1	50.0	1014	Lincor	
4G/3G	1710~2200	MIMO 1	45	-3.5	1.9	50 Ω	10W	Linear	Omni-Directional
Band 1,2,3,4,9,23,25,35,39,66	1/10*2200	MIMO 2	40.3	-4.1	1.5				
4G/3G	2400~2600	MIMO 1	42.3	-3.8	1.6				
Band 7,38,41	2490~2690	MIMO 2	47.8	-3.3	3				
5G NR		MIMO 1	18.1	-7.8	-0.6				
Band 22,42,48,77,78,79	3300~5000	MIMO 2	16.9	-8.5	-1.6				
LTE5200/		MIMO 1	25.7	-5.9	-0.9				
Wi-Fi 5800	5150~5925	MIMO 2	34.7	-4.6	3.4				

Mechanical		
Casing	PCL1250Y	
Coaxial Cable	CFD-200	
Cable Length	1 Meter Standard, fully customizable	
Connector	SMA Male Standard, fully customizable	
Weight	400g (Antenna with 1 meter Cable and Stand)	
Dimension	164*164*36.5mm	
Waterproof Rating	IP67	
Magnetic Pull Force	11.24 kgF-cm	
Magnetic Dim/Pcs	Ø18*3t N48M/ 8 pcs	



Environmental	
Temperature Range	-40°C to 85°C
Humidity	Non-condensing 65°C 95% RH




		5G/4G Bands			
Band Number	Band Number 5GNR / FR1 / LTE / LTE-Advanced / WCDMA / HSPA / HSPA+ / TD-SCDMA / Cat M / NB-IoT				
	Uplink	Downlink	Covered		
1	UL: 1920 to 1980	DL: 2110 to 2170	\checkmark		
2	UL: 1850 to 1910	DL: 1930 to 1990	\checkmark		
3	UL: 1710 to 1785	DL: 1805 to 1880	\checkmark		
4	UL: 1710 to 1755	DL: 2110 to 2155	\checkmark		
5	UL: 824 to 849	DL: 869 to 894	\checkmark		
7	UL: 2500 to 2570	DL:2620 to 2690	\checkmark		
8	UL: 880 to 915	DL: 925 to 960	\checkmark		
9	UL: 1749.9 to 1784.9	DL: 1844.9 to 1879.9	\checkmark		
11	UL: 1427.9 to 1447.9	DL: 1475.9 to 1495.9	\checkmark		
12	UL: 699 to 716	DL: 729 to 746	\checkmark		
13	UL: 777 to 787	DL: 746 to 756	\checkmark		
14	UL: 788 to 798	DL: 758 to 768	\checkmark		
17	UL: 704 to 716	DL: 734 to 746	\checkmark		
18	UL: 815 to 830	DL: 860 to 875	\checkmark		
19	UL: 830 to 845	DL: 875 to 890	\checkmark		
20	UL: 832 to 862	DL: 791 to 821	\checkmark		
21	UL: 1447.9 to 1462.9	DL: 1495.9 to 1510.9	\checkmark		
22	UL: 3410 to 3490	DL: 3510 to 3590	\checkmark		
23	UL:2000 to 2020	DL: 2180 to 2200	\checkmark		
24	UL:1625.5 to 1660.5	DL: 1525 to 1559	\checkmark		
25	UL: 1850 to 1915	DL: 1930 to 1995	\checkmark		
26	UL: 814 to 849	DL: 859 to 894	\checkmark		
27	UL: 807 to 824	DL: 852 to 869	\checkmark		
28	UL: 703 to 748	DL: 758 to 803	\checkmark		
29	UL: -	DL: 717 to 728	\checkmark		
30	UL: 2305 to 2315	DL: 2350 to 2360	\checkmark		
31	UL: 452.5 to 457.5	DL: 462.5 to 467.5	×		
32	UL: -	DL: 1452 – 1496	\checkmark		
35		1850 to 1910	\checkmark		
38		2570 to 2620	\checkmark		
39		1880 to 1920	√		
40		2300 to 2400	√		
41		2496 to 2690	\checkmark		
42		3400 to 3600	×		
43		3600 to 3800	√		
48		3550 to 3700	√		
66	UL: 1710-1780	DL: 2110-2200	√		
71		617 to 698	√		
74/75/76		1427 to 1518	1		
77		3300 to 4200	\checkmark		
78		3300 to 3800	×		
79		4400 to 5000	\checkmark		








3.




3.2 Efficiency






3.3 Peak Gain















Free space





4G MIMO 1 - 3D and 2D Radiation Patterns

704MHz

































4.3 4G MIMO 2 - 3D and 2D Radiation Patterns































Mechanical Drawing (Units: mm)

5.





PE Bag

110mm

Packaging


6.

LMA101.A.BI.001

Packaging Specifications

1pc LMA101.A.BI.001 per small box Box Dimensions - 235*170*110mm Weight - 650g

5 small boxes in one carton Carton Dimensions - 360*290*260mm Weight - 3.8Kg




235mm

22 21.7

170mm


Pallet Dimensions 1100*1100*1290mm 48 Cartons per Pallet 12 Cartons per layer 4 Layers

1290mm










Cable




7.3 Wall Mount





8. Installation

Testing setup 8.1



Max Pull Force: 11.24Kgf-cm



Changelog for the datasheet

SPE-17-8-017 – LMA101.A.BI.001			
Revision: E (Current	Version)		
Date:	2023-07-10		
Changes:	Update electrical specifications		
Changes Made by:	Cesar Sousa		

Previous Revisions

Revision: D		
Date:	2019-01-02	
Changes:	Updated to show 5G data	
Changes Made by:	Jack Conroy	

Revision: C		
Date:	2018-12-20	
Changes:	Updated Drawing issues	
Changes Made by:	Jack Conroy	

Re	Revision: B				
	Date:	2017-06-15			
	Changes:	Updated to match PCN			
	Changes Made by:	Andy Mahoney			

Revision: A (Original First Release)		
Date:	2017-02-23	
Notes:		
Author:	Jack Conroy	



www.taoglas.com