

APRA2504G3Z

Request Samples



Check Inventory (>)



25.1 x 25.1 x 4.0 mm RoHS/RoHS II Compliant MSL Level = 1

Features

- Complies with Automotive Qualification (AEC-Q200)
- Complies with IATF 16949 Certification
- Multiband GNSS patch with GPS/GLONASS/BeiDou/Galileo
- Low Return Loss
- RHCP polarization
- Wide operating temperature (-40°C to +105°C)
- Peak Gain of 3.5 dBi
 - o GPS: 1.5 dBi
 - o GLONASS: 3.5 dBi
 - o BeiDou: 2.5 dBi

Applications

- GNSS applications
- Automotive
- IoT, M2M, V2X
 - Industrial IoT
 - o Infrastructure IoT
 - Consumer IoT
- Navigation
- Logistics
- Geofencing
- Remote monitoring
- Surveying and mapping systems

Product Image







APRA2504G3Z

Request Samples (>)



Check Inventory (>)



25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

Electrical Specifications

Parameter	Specification		Unit	
Operating Band	BeiDou	GPS / Galileo	GLONASS	
Operating Frequency	1561.098 ± 2.046	1575.42 ± 1.023	1602 ± 5	
Center Frequency	1586 ± 3			MHz
Bandwidth	65			
Gain	2.5	1.5	3.5	dBi
Max VSWR	3.0			
Impedance	50		Ω	
Polarization	RHCP			

Note:

- Ground Plane size: 70 x 70 mm
- Actual Electrical Value will depend on the size of ground plane in use

Mechanical Specifications

Parameter	Specification	
Antenna Dimension	25.1 x 25.1 x 4.0 mm	
Material	Ceramic	
Termination	Silver	
Mounting Type	Through-Hole + Adhesive Tape	

Environmental Specifications

Parameter	Specification	
Operating Temperature	-40°C to +105°C	
Storage Temperature		
Frequency Temperature Coefficient (T _f)	-40° C to $+105^{\circ}$ C $(0 \pm 20 \text{ ppm/}^{\circ}$ C)	
RoHS / RoHS II Compliant	Yes	
MSL	1	
Environmentally Friendly	Pb free	
Relative Humidity	0~95%	





APRA2504G3Z

Request Samples (>)



Check Inventory (>)





25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1


Product Marking



Product Dimension







Unit: mm





APRA2504G3Z






Check Inventory (>)



25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1


Layout Dimensions



UNIT:mm

Unit: mm

Tape Dimensions



Double – coated thin adhesive tape | Thickness: 0.12 mm

Unit: mm





APRA2504G3Z

Request Samples (>)




Check Inventory (>)




25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

VNA Test Measurement – Set up




Radiation Measurement - Set up





YZ-Plane







APRA2504G3Z

Request Samples




Check Inventory (>)



25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

Test Measurement – Return Loss







APRA2504G3Z

Request Samples (>)




Check Inventory (>)



25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

Radiation Measurement - 2D Pattern

XZ + YZ Plane : GPS







APRA2504G3Z

Request Samples (>)




Check Inventory (>)



25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

XZ + YZ - Plane : BeiDou







APRA2504G3Z

Request Samples (>)




Check Inventory (>)



25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

XZ + YZ - Plane : GLONASS







APRA2504G3Z

Request Samples



Check Inventory (>)



25.1 x 25.1 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

Soldering Condition

Soldering should be done in 6 seconds by a feed pin of maximum temperature +400 °C.

Precautions

- Do not direct solder onto the silver electrode of the antenna pattern.
- Do not use the patch antenna in a corrosive gaseous atmosphere for example sulfur gas, chlorine gas.





APRA2504G3Z

Request Samples



Check Inventory (>)




25.1 x 25.1 x 4.0 mm RoHS/RoHS II Compliant MSL Level = 1


Packaging Information


Dimensions of the Outer Carton: $330 \times 280 \times 254 \text{ mm}$ ($200 \times 4 = 800 \text{ pcs}$ each)


Dimensions of the Inner Carton: 261 x 152 x 118 mm (200 pcs each)














ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

