



Description: 25x25x12 GNSS+L5 Active Antenna

PART NUMBER: ANT1825JB01BGNL5A

Features:

- Size: 25x25x12 mm³
- High radiation efficiency
- Low noise figure
- · RoHS compliant

Applications:

- Navigation device
- Telematics box
- Fleet management

SPECIFICATIONS

Ceramic Patch Antenna

DESCRIPTION	VALUE
Dimension	25×25×9.0 mm³
	L5 Band : 1176.45 MHz
Contro Fraguency	BD: 1561 MHz
Centre Frequency	GPS: 1575.42 MHz
	GLONASS: 1602 MHz
	L5 Band:1176.45 ± 10MHz
Bandwidth	BD: 1561 ± 2MHz
Balluwidili	GPS: 1575.42 ± 2MHz
	GLONASS: 1602 ± 4 MHz
	L5 Band: 2.36 dBic
Peak Gain	BD: 1.26 dBic
reak Gaiii	GPS: 1.81 dBic
	GLONASS: 1.63 dBic
VSWR	2.0 Max.
Polarization	Right Hand Circular Polarization

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:



Description: 25x25x12 GNSS+L5 Active Antenna

PART NUMBER: ANT1825JB01BGNL5A

SPECIFICATIONS

LNA

DESCRIPTION		VALUE
Centre Frequency		L5 Band: 1176.45 MHz
		BD: 1561 MHz
		GPS: 1575.42 MHz
		GLONASS: 1602 MHz
Gain		L5 Band: 38 ± 3 dB
		$BD: 38 \pm 3 dB$
		GPS: 38 ± 3 dB
		GLONASS: 38 ± 3 dB
		40dB min 1.0 ~ 960 MHz
SAW Filter (Out of Band Attenuation) SAW Filter (Out of Band Attenuation)	/ /	25dB min 1427~1463 MHz
	BD / GPS / GLONASS:	25dB min 1710~1785 MHz
		25dB min 1850~1980 MHz
		40dB min 2401~2483 MHz 20dB min 1.0 ~ 960 MHz
		25dB min 1427~1463 MHz
	L5:	30dB min 1710~1785 MHz
	-	30dB min 1850~1980 MHz
		40dB min 2401~2483 MHz
Output VSWR		2.0 (Max.)
Noise Figure		< 1.5 dB
Supply Voltage		3.0 ~ 3.6 V
Current Consumption		15 mA (Max.)
Output Impedance		50Ω
Operating Temperature		-30 ~ +85 °C
Humidity		< 95%
Storage Temperature		-40 ~ +90 °C

NOTE

- 1. Based on 50×50 mm² ground plane (free space)
- 2. Centre frequency will be offset to working frequency while changes of customer's housing and ground plane.
- 3. Please contact local sales if you need customized design to gain optimum antenna performance.


ROHS



Description: 25x25x12 GNSS+L5 Active Antenna

PART NUMBER: ANT1825JB01BGNL5A

MECHANICAL DRAWING



Length	25.0 ± 0.3 mm
Width	25.0 ± 0.3 mm
Thickness	12 mm (MAX.)
Cable	Diameter = 1.13 mm; Length = 100 mm ± 2 mm; Black
Connector	I-PEX Connector 20278



TECHNICAL DATA SHEET

Description: 25x25x12 GNSS+L5 Active Antenna

PART NUMBER: ANT1825JB01BGNL5A

REVISION HISTORY

Revision	Date	Description
Version 1	Feb 8 2021	- New issue for Pulse version