PRODUCT SPECIFICATION

[1. SCOPE]
This specification covers the 4.8mm PITCH WIRE TO WIRE CONNECTOR series.

[2. PRODUCT NAME AND PART NUMBER]

Product Name	Part Number	
Female Terminal (AWG #18~24)	5005T,TL	
Female Terminal (AWG #24~28)	5009T,TL	
Male Terminal (AWG #18~24)	5006T,TL	
Male Terminal (AWG #24~28)	5008T,TL	
Receptacle Housing	5025-NR1	
Plug Housing (With Mounting Ears)	5025-NP	
Plug Housing (Without Mounting Ears)	5025-NP1	

N: Number of Circuits Refer to the attached drawing.

[3. RATINGS AND APPLICABLE WIRES]

l tem	Standard			
Rated Voltage (MAX.)	250V [AC (rms) / DC]			
	5205T,TL	FA	Insulation 0.D.: \$\phi 3.4mm MAX.	
Rated Current (MAX.)*1	5206T,TL	5206T,TL		
and Applicable wires	5005T,TL	- 5A	Insulation 0.D.: \$\phi_3.0mm MAX.	
	5006T,TL	JA		
	5008T,TL	- 3A	Insulation 0.D.:	
	5009T,TL] 3A	ϕ 2.4mm MAX.	
Ambient Temperature Range	-40°C ~ +105°C*2			

*1 : When used maximum size wire.

\$2: Including terminal temperature rise.

5025(T)

[4. PERFORMANCE] 4-1. Electrical Performance:

1	Item Test Condition		Requirement	
4-1-1	Contact resistance	Mate connectors measure by dry circuit, 20mV max., 10mA.	10m Ω MAX. 1000M Ω MIN.	
4-1-2	Insulation Resistance	Mate connectors, apply 500V DC between adjacent terminal or ground		
4-1-3	Dielectric Strength	Mate connectors, apply 1500V AC for 1 minute between adjacent terminal or ground	No breakdown	
4-1-4	Contact Resistance on Crimped Portion	Crimp the applicable wire on to the terminal, measure by dry circuit, 20mV MAX., 10mA.	5mΩ MAX.	

4-2. Mechanical Performance:

ltem		Test Condition	Requirement		
4-2-1	Insertion and Withdrawal Force	Insert and withdraw connectors at the speed rate of 25±3mm/minute	Refer to paragraph 6		
na p			AWG #14 10.0 Kgf MIN.		
4-2-2 Crimping Pull Out Force		AWG #16 10.0 Kgf MIN.			
		AWG #18 10.0 Kgf MIN.			
	Pull Out	Fix the crimped terminal, apply axial pull out force on the wire at the speed rate of 25±3mm/minute	AWG #20 6.8 Kgf MIN.		
			AWG #22 5.5 Kgf MIN.		
			AWG #24 3.6 Kgf MIN.		
			AWG #26 2.7 Kgf MIN.		
		AWG #28 1.4 Kgf MIN.			
4-2-3	Terminal Insertion Force	Insert the crimped terminal into the housing	2.0 Kgf MAX.		
4-2-4	Terminal/ Housing Retention Force	Apply axial pull out force at the speed rate of 25± 3mm/minute on the terminal assembled in the housing	7.0 Kgf MIN.		

4-3. ENVIRONMENTAL PERFORMANCE AND OTHERS

ltem		Test Condition	Requirement	
4-3-1	Repeated Insertion/ Withdrawal	When mated up to 30 cycles Contact repeatedly by the rate of Resistance 10 cycles per minuite		20mΩ MAX.
4-3-2	Temperature Rise	Carrying rated current load	30°C MAX.	
		1 1 1 1 1 1 5 mm D D	Appearance	No Damage
4-3-3 Vibration	 Vibration	Amplitude: 1.5mm P-P Sweep time: 10-55-10 Hz in 1 minute	Contact Resistance	20m Ω MAX.
		Duration: 2 hours in each X.Y.Z. axes	Dis- continuity	$1 \mu \text{ sec.}$
			Appearance	No Damage
4-3-4 Shock	Shock	50G, 3 strokes in each	Contact Resistance	20mΩ MAX.
		X.Y.Z. axes	Dis- continuity	1μ sec
4-3-5 Heat Resistance		405 1085 00 1	Appearance	No Damag
		105±2°C, 96 hours	Contact Resistance	20m Ω MAX.
		40 1000 00 1	Appearance	No Damag
4-3-6	Cold Resistance	-40±3°C, 96 hours	Contact Resistance	20mΩ MAX.
			Appearance	No Damag
4-3-7 Humidity		Temperature: 60 ± 2°C	Contact Resistance	20mΩ MAX.
	Humidity 	Relative Humidity: 90~95% Duration: 96 hours	Dielectric Strength	Must mee
			Insulation Resistance	:
		5 cycles:	Appearance	No Damag
4-3-8	4-3-8 Temperature a) - 55°C 30 MIN. Cycling b) +105°C 30 MIN.		Contact Resistance	20mΩ MAX.

5025(T)

Item		Test Condition	Requirement	
		48 hours exposure to a salt	Appearance	No Damage
4-3-9	Salt spray from the 5% solution Spray at 35°C	Contact Resistance	20m Ω MAX.	
4-3-10 SO ₂ Gas	04 50 50 50	Appearance	No Damage	
	24 hours exposure to 50 ppm. SO ₂ gas at 40°C	Contact Resistance	20mΩ MAX.	

[5. PRODUCT SHAPE, DIMENSIONS AND MATERIALS] Refer to the attached drawing.

[6: INSERTION/WITHDRAWAL FORCE]

(kgf)

CKT SIZE	Insertion (MAX.)			Withdrawal (MIN.)		
	Initial	6th.	30th.	Initial	6th.	30th.
2	4.0	3.6	2.8	0.30	0.20	0.20
3	6.0	5.4	4.2	0.45	0.30	0.30
4	8.0	7.2	5.6	0.60	0.40	0.40
6	12.0	10.8	8.4	0.90	0.60	0.60
9	18.0	16.2	12.6	1.35	0.90	0.90
12	24.0	21.6	16.8	1.80	1.20	1.20
15	30.0	27.0	21.0	2.25	1.50	1.50