


CODING BOARD			
ORIGINALS		COMPLEMENTARY CODING	
BROWN		GREY	
GREEN		BLUE	
WHITE		MALE HOUSING NOT AVAILABLE FOR COMPLEMENTARY CODING MECHANICAL SETTINGS CAN BE DIFFERENT FROM ORIGINAL CODING TO COMPLEMENTARY ONES.	
BLACK			

AREA FOR CONNECTOR ASSEMBLY
Scale: 1:1



NOTES:

- CAVITY PREINT MUST NOT GET OUTSIDE THE BOTTOM OF THE PREINT
- NO BURR ADMITTED IN THAT AREA
- 3 RADIUS WITHOUT DIMENSIONS R=0.5 MAX

Recommended Plastic Material: >PBT-GF20<
 Recommended Metal Material: CuSn6 or CuFe2
 Plating: 0.84µm to 3.34µm minus of pure tin (Sn)
 1.34µm mini Nickel (Ni) underlayer.

FIRST RELEASE EC NO: G2005-0319 DRAWING: GDESBRUERES 2005/04/27 CHKD: JLDUCLOS 2005/04/27 APPROVAL: LSTICKEIR 2005/04/28	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED) <table border="1"> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> <tr> <td>4 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>3 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>2 PLACES</td> <td>± 0.10</td> <td>± ---</td> </tr> <tr> <td>1 PLACE</td> <td>± 0.2</td> <td>± ---</td> </tr> </table>		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± 0.10	± ---	1 PLACE	± 0.2	± ---	DIMENSION STYLE MM ONLY	SCALE 5:1	DESIGN UNITS METRIC	FIRST ANGLE PROJECTION
			mm	INCH																	
	4 PLACES	± ---	± ---																		
	3 PLACES	± ---	± ---																		
2 PLACES	± 0.10	± ---																			
1 PLACE	± 0.2	± ---																			
DESCRIPTION INTERFACE DRAWING MOX RCPT HSG DR 3CKT 98298 SERIES#	DRAWN BY GDESBRUERES 2005/04/13	DATE 2005/04/13	CHECKED BY JLDUCLOS 2005/04/15	DATE 2005/04/15	MOLEX INCORPORATED MATERIAL NO. SD-98298-003																
MATERIAL NO. SD-98298-003	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SHEET NO. 1 OF 1																
INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																					