

Multilayer Ceramic Chip Capacitor

Part Number: 2211JA250102JGTSYX

Description: 2211 250Vac (Y2), 305Vac (X1), 50/60Hz / 1000Vdc 1.0nF ±5% C0G/NP0 (1B)

IEC/EN60384-14:2013+A1 Approval


Specifications: UL60384-14, CAN/CSA E60384-14:14

TÜV R60153659 / ID11111233476 Certification:

UL/cUL E228790-20201127

IEC/EN 60384-14:2013+A1 Class Y2 / X1 Classification:

UL/cUL FOWX2, FOWX8



Component Marking and Certification Bodies:



Material Group I: CTI >= 600

Nominal Capacitance Value

Mechanical Specification

Size Code 2211

 $5.7 \pm 0.40 \ (0.225 \pm 0.016)$ Length (L1) in mm (") Width (W) in mm (") $2.79 \pm 0.30 (0.11 \pm 0.012)$

Thickness (T) in mm (") 2.80 Max (0.11 Max)

0.50 (0.020) Minimum Termination Band (L2,L3) in mm (") Maximum Termination Band (L2,L3) in mm (") 0.80 (0.030) Minimum Band Gap (L4) in mm (") 4.0 (0.158)

Nickel Barrier, Sn Plated Solder (RoHS compliant) **Termination Material**

Solderability IEC-60068-2-58

7" Reel Horizontal Orientation, 500 per reel Packaging

General Electrical Specification

Rated Voltage Class Y2 (250Vac), Class X1 (305Vac), 50/60Hz, 5kV impulse

Humidity Grade Grade III (IEC/EN60384-14:2013 Annex 1)

Maximum DC Working Voltage 1000Vdc certified / (2500Vdc outside scope of any specification)

1.0nF

Capacitance Tolerance +5%

≤0.0015 Tangent of Loss Angle (Tan δ)

Capacitance and Tan δ Test Conditions 1.0Vrms @ 1MHz Voltage Proof

100% test: 4000Vdc 1s min / 5s max

AQL test: 4000Vdc / 3000Vac 60s min / 5kV 1.2x50µs impulse (50mA max charging current for DC tests)

Min Insulation Resistance (IR) 100.00GOhm @ 100Vdc

C0G/NP0 (1B) Dielectric Classification -55°C / +125°C Rated Temperature Range

No DC Voltage 0±30ppm/°C Maximum Capacitance Change over Temperature Range

Rated DC Voltage -

Climatic Category (IEC) 55/125/56 Ageing Characteristic Zero

Knowles Precision Devices - Sales

Europe: KPD-Europe-sales@knowles.com Asia: KPD-Asia-sales@knowles.com

USA: KPD-NA-sales@knowles.com www.knowlescapacitors.com

The information contained on this drawing is confidential and may not be copied in whole or part ir any form or disclosed to a third party without the consenof Knowles and any customer mentioned within this specification.

Data is correct to the best of our knowledge, errors and

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data

for this part may differ and is available at http://www.knowlescapacitors.com or by contacting us.

Date: Thursday, September 02, 2021



Multilayer Ceramic Chip Capacitor

Part Number: 2211JA250102JGTSYX

Description: 2211 250Vac (Y2), 305Vac (X1), 50/60Hz / 1000Vdc 1.0nF ±5% C0G/NP0 (1B)

Environmental

RoHS Compliant to 2011/65/EC as amended by 2015/863/EU

Compliant

REACH Compliant

211 compliant

California Proposition 65

No exposure risk


Board Layout

Knowles' conventional 2-terminal chip capacitors generally be mounted using pad designs in accordance with international specification IPC-7351, Generic Requirements for Surface Mount Design and Land Pattern Standards, but there are some other factors that have been shown to reduce mechanical stress, such as reducing the pad width to less than the chip width. In addition, the position of the chip on the board should be considered.

Some high voltage parts may require modifications to the board layout and/or the addition of a conformal coating to prevent flashover. Refer to application note AN0043 for further information.

IPC-7351 pad design


	2211	
С	5.40mm	0.213"
Υ	1.35mm	0.053"
Х	3.10mm	0.122"



Packaging

Tape packaging information for tape-and-reel parts:

Tape and reel packing of surface mounting chip capacitors for automatic placement are in accordance with IEC60286-3.




Soldering

Reflow solder in accordance with IPC-A-610. Recommended reflow profile as laid down in IPC/JEDEC J-STD-020.

Wave soldering is also possible, but care must be taken for case sizes 1210 and larger and component thickness >1.0mm. Trials are encouraged.

Hand soldering is not recommended and can lead to component damage through thermal shock.

DLI



Application notes with mounting and handling guidance are available on request.

Johanson MFG

Knowles Precision Devices - Sales

This datasheet is for a standard item and is confirmed valid on the date generated, the latest published data for this part may differ and is available at http://www.knowlescapacitors.com or by contacting us.

Europe: KPD-Europe-sales@knowles.com Asia: KPD-Asia-sales@knowles.com

Compex

USA: KPD-NA-sales@knowles.com

www.knowlescapacitors.com

The information contained on this drawing is confidential and may not be copied in whole or part in

Novacap

any form or disclosed to a third party without the consenof Knowles and any customer mentioned within this specification.

Data is correct to the best of our knowledge, errors and

omissions excepted.

Syfer

Date: Thursday, September 02, 2021

Voltronics