TECHNICAL DATA SHEET



Description: 1608 1.5&2.4GHz Diplexer

PART NUMBER: DPX1608LL88R1524A

Features:

- Size : 1.6 x 0.8 x 0.6 mm
- · RoHS compliant

Applications:

• LTE (0.7~2.7GHz)

ELECTRICAL SPECIFICATIONS

DESCRIPTION	VALUE		
Pass Band	Low Band	High Band	
	1559-1610 MHz	2400-2500 MHz	4900-6000 MHz
Insertion Loss	0.6dB (Typ)	0.7dB (Typ)	0.6dB (Typ)
V.S.W.R / Return-Loss	2.0 (Max) / 10.0 dB (Min)	2.0 (Max) / 10.0 dB (Min)	2.0 (Max) / 10.0 dB (Min)
Attenuation	18dB (Min).@2400~2500MHz	20dB (Min).@1575~1610MHz	
	15dB (Min).@4900~6000MHz		
Operating Temperature	-40~+85°C		

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION



This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and rederal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:

Pulse Worldwide Headquarters 15255 Innovation Drive #100 San Diego, CA 92128 USA Tel:1-858-674-8100 Pulse/Larsen Antennas 18110 SE 34th St Bldg 2 Suite 250 Vancouver, WA 98683 USA Tel: 1-360-944-7551 Europe Headquarters Pulse GmbH & Do, KG Zeppelinstrasse 15 Herrenberg, Germany Tel: 49 7032 7806 0 Pulse (Suzhou) Wireless Products Co, Inc. 99 Huo Ju Road(#29 Bldg,4th Phase Suzhou New District Jiangsu Province, Suzhou 215009 PR China Tel: 86 512 6807 9998 1

TECHNICAL DATA SHEET



Description: 1608 1.5&2.4GHz Diplexer

PART NUMBER: DPX1608LL88R1524A

MECHANICAL DRAWING

	DIMENSIONS
L (mm)	1.60 ± 0.15
W (mm)	0.80 ± 0.15
T (mm)	0.60 ± 0.15
P1 (mm)	0.20 ± 0.15
P2 (mm)	0.20 ± 0.15
P3 (mm)	0.20 ± 0.15
P4 (mm)	0.20 ± 0.15
P5 (mm)	0.20 ± 0.15
P6 (mm)	0.20 ± 0.15
D1 (mm)	0.20 ± 0.15
D2 (mm)	0.30 ± 0.10
D3 (mm)	0.15 ± 0.10




Fig. 1 Filter outlines

TERMINATION CONFIGURATION

P1	GND
P2	Common
P3	GND
P4	High Band
P5	GND
P6	Low Band

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and otherst te and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden.



Pulse | LARSEN Antennas

TECHNICAL DATA SHEET

Description: 1608 1.5&2.4GHz Diplexer

PART NUMBER: DPX1608LL88R1524A




Fig. 2 Reference design of evaluation board

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

CONFIDENTIAL AND PROPRIETARY INFORMATION **CONFIDENTIAL** AND PROPRIETARY INFORMATION OF Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other **CONFIDENTIAL** HAVE AND PROPRIETARY INFORMATION OF Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other **CONFIDENTIAL** HAVE AND PROPRIETARY INFORMATION OF Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other **CONFIDENTIAL** HAVE AND PROPRIETARY INFORMATION OF Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other **CONFIDE** HAVE AND PROPRIETARY INFORMATION OF PULSE IS STRICTLY DISCIDLE. TO PROVIDE AND PROPRIETARY INFORMATION OF PULSE IS STRICTLY FORDIDATE. TO PROVIDE AND PROPRIETARY INFORMATION OF PULSE IS STRICTLY FORDIDATE. TO PROVIDE AND PROPRIETARY INFORMATION OF PULSE IS STRICTLY FORDIDATE. TO PROVIDE AND PROPRIETARY INFORMATION OF PULSE IS STRICTLY FORDIDATE. TO PROVIDE AND PROVIDE AND PROPRIETARY INFORMATION OF PULSE IS STRICTLY FORDIDATE. TO PROVIDE AND PROPRIETARY INFORMATION OF PULSE IS STRICTLY FORDIDATE. TO PROVIDE AND PROVIDE AND PROPRIETARY INFORMATION OF PULSE IS STRICTLY FORDIDATE. TO PROVIDE AND PROVIDE

TECHNICAL DATA SHEET



Description: 1608 1.5&2.4GHz Diplexer

PART NUMBER: DPX1608LL88R1524A

ELECTRICAL PERFORMANCES




Fig. 3 Frequency Characteristics

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

CONFIDENTIAL AND PROPRIETARY INFORMATION **ROHS** 4 This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. Pulse LARSEN Antennas

TECHNICAL DATA SHEET

Description: 1608 1.5&2.4GHz Diplexer

PART NUMBER: DPX1608LL88R1524A

REVISION HISTORY

Revision	Date	Description
Version 01	Feb. 1, 2021	- New issue

In the effort to improve our products, we reserve the right to make changes judged to be necessary.

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and Its receipt or possession does not convey any rights to reproduce, disclose its contexts, protected by copyright, trade secret and other state and te and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden.



5