

# BLA1011-2

Avionics LDMOS transistor

Rev. 6 — 6 May 2013

Product data sheet

## 1. Product profile

### 1.1 General description

Silicon N-channel enhancement mode LDMOS transistor encapsulated in a 2-lead flangeless package (SOT538A) with a ceramic cap. The common source is connected to the mounting base.

**Table 1. Typical performance**

*RF performance at  $T_h = 25\text{ °C}$  in a common source test circuit.*

Mode of operation	f (MHz)	V <sub>DS</sub> (V)	P <sub>L</sub> (W)	G <sub>p</sub> (dB)
Pulsed class-AB; $t_p = 50\text{ }\mu\text{s}$ ; $\delta = 2\%$	1030 to 1090	36	2	>16

#### CAUTION



This device is sensitive to ElectroStatic Discharge (ESD). Therefore care should be taken during transport and handling.

### 1.2 Features and benefits



- High power gain
- Easy power control
- Excellent ruggedness
- Source on mounting base eliminates DC isolators, reducing common mode inductance.

### 1.3 Applications

- Avionics applications in the 1030 to 1090 MHz frequency range.

## 2. Pinning information

**Table 2. Pinning**

Pin	Description	Simplified outline	Graphic symbol
1	drain		 sym112
2	gate		
3	source, connected to mounting base		



### 3. Ordering information

**Table 3. Ordering information**

Type number	Package		Version
	Name	Description	
BLA1011-2	-	ceramic surface mounted package; 2 leads	SOT538A

### 4. Limiting values

**Table 4. Limiting values**

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions	Min	Max	Unit
$V_{DS}$	drain-source voltage		-	75	V
$V_{GS}$	gate-source voltage		-	±15	V
$I_D$	drain current (DC)		-	2.2	A
$P_{tot}$	total power dissipation	$T_h \leq 25\text{ °C}$		10	W
$T_{stg}$	storage temperature		-65	+150	°C
$T_j$	junction temperature		-	200	°C

### 5. Thermal characteristics

**Table 5. Thermal characteristics**

Symbol	Parameter	Conditions	Typ	Unit
$Z_{th(j-mb)}$	thermal impedance from junction to mounting base		[1] 1	K/W
$R_{th(mb-h)}$	thermal resistance from mounting base to heatsink		[2] 6.5	K/W

[1] Thermal impedance is determined under RF operating conditions with pulsed bias and  $T_h = 25\text{ °C}$ .

[2] Typical value for mounting on PCB with 32 0.4 mm thermal vias with 20  $\mu\text{m}$  tin plating and thermal compound between PCB and heatsink.

### 6. Characteristics

**Table 6. Characteristics**

$T_j = 25\text{ °C}$  unless otherwise specified.

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
$V_{(BR)DSS}$	drain-source breakdown voltage	$V_{GS} = 0$ ; $I_D = 0.2\text{ mA}$	75	-	-	V
$V_{GSth}$	gate-source threshold voltage	$V_{DS} = 10\text{ V}$ ; $I_D = 20\text{ mA}$	2	-	5	V
$I_{DSS}$	drain-source leakage current	$V_{GS} = 0$ ; $V_{DS} = 26\text{ V}$	-	-	0.1	mA
$I_{DSX}$	on-state drain current	$V_{GS} = V_{GSth} + 9\text{ V}$ ; $V_{DS} = 10\text{ V}$	2.8	-	-	A
$I_{GSS}$	gate leakage current	$V_{GS} = \pm 15\text{ V}$ ; $V_{DS} = 0$	-	-	40	nA

**Table 6. Characteristics ...continued** $T_j = 25\text{ }^\circ\text{C}$  unless otherwise specified.

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
$g_{fs}$	forward transconductance	$V_{DS} = 10\text{ V}; I_D = 0.75\text{ A}$	-	0.5	-	S
$R_{DSon}$	drain-source on-state resistance	$V_{GS} = 10\text{ V}; I_D = 0.75\text{ A}$	-	1.2	-	$\Omega$
$C_{is}$	input capacitance	$V_{GS} = 0\text{ V}; V_{DS} = 26\text{ V}; f = 1\text{ MHz}$	-	11	-	pF
$C_{os}$	output capacitance	$V_{GS} = 0\text{ V}; V_{DS} = 26\text{ V}; f = 1\text{ MHz}$	-	9	-	pF
$C_{rs}$	feedback capacitance	$V_{GS} = 0\text{ V}; V_{DS} = 26\text{ V}; f = 1\text{ MHz}$	-	0.5	-	pF

## 7. Application information

**Table 7. RF performance in a common source class-AB circuit** $T_h = 25\text{ }^\circ\text{C}; R_{th\ mb-h} = 6.5\text{ K/W}$  unless otherwise specified.


Mode of operation	f	$V_{DS}$	$I_{DQ}$	$P_L$	$G_p$	$t_r$	$t_f$	Pulse droop
	(MHz)	(V)	(mA)	(W)	(dB)	(ns)	(ns)	(dB)
Pulsed class-AB; $t_p = 50\text{ }\mu\text{s}; \delta = 2\%$	1030 to 1090	36	50	2	>16	<15	<15	<0.5

### 7.1 Ruggedness in class-AB operation

The BLA1011-2 is capable of withstanding a load mismatch corresponding to VSWR = 5 : 1 through all phases under the operating conditions.

**Table 8. Typical impedance values**


Frequency (MHz)	$Z_S$ ( $\Omega$ )	$Z_L$ ( $\Omega$ )
1030	$1.51 + j 11.76$	$6.9 + j 5$
1060	$1.51 + j 11.26$	$6.7 + j 5.9$
1090	$1.52 + j 10.77$	$5.1 + j 6.6$



$T_h = 25\text{ }^\circ\text{C}$ ;  $V_{DS} = 36\text{ V}$ ;  $I_{DQ} = 50\text{ mA}$ ; class-AB;  $t_p = 50\text{ }\mu\text{s}$ ;  $\delta = 2\%$ .

- (1)  $f = 1060\text{ MHz}$ .
- (2)  $f = 1030\text{ MHz}$ .
- (3)  $f = 1090\text{ MHz}$ .


**Fig 1. Load power as a function of drive power; typical values.**



$T_h = 25\text{ }^\circ\text{C}$ ;  $V_{DS} = 36\text{ V}$ ;  $I_{DQ} = 50\text{ mA}$ ; class-AB;  $t_p = 50\text{ }\mu\text{s}$ ;  $\delta = 2\%$ .

- (1)  $f = 1060\text{ MHz}$ .
- (2)  $f = 1030\text{ MHz}$ .
- (3)  $f = 1090\text{ MHz}$ .


**Fig 2. Power gain as a function of load power; typical values.**



$T_h = 25\text{ }^\circ\text{C}$ ;  $V_{DS} = 36\text{ V}$ ;  $I_{DQ} = 50\text{ mA}$ ; class-AB;  $t_p = 50\text{ }\mu\text{s}$ ;  $\delta = 2\%$ .


- (1)  $P_L = 1\text{ W}$ .
- (2)  $P_L = 2\text{ W}$ .
- (3)  $P_L = 3\text{ W}$ .
- (4)  $P_L = 4\text{ W}$ .

**Fig 3. Power gain as a function of frequency; typical values.**



$T_h = 25\text{ }^\circ\text{C}$ ;  $V_{DS} = 36\text{ V}$ ;  $I_{DQ} = 50\text{ mA}$ ; class-AB;  $f = 1090\text{ MHz}$ ;  $t_p = 50\text{ }\mu\text{s}$ ;  $\delta = 2\%$ .

**Fig 4. Load power as a function of gate-source voltage; typical values.**



Dimensions in mm.

The components are situated on one side of the Rogers 6006 printed-circuit board (thickness = 0.64 mm;  $\epsilon_r = 6.2$ ), the other side is unetched and serves as a ground plane. Earth connections from the component side to the ground plane are made by through-metallization.

**Fig 5. Printed-circuit board for class-AB test circuit.**

## 8. Test information

**Table 9. List of components for class-AB test circuit**  
(see [Figure 5](#))

Component	Description	Value
C1, C8	multilayer ceramic chip capacitor	[1] 56 pF
C2	multilayer ceramic chip capacitor	[1] 7.5 pF
C3	multilayer ceramic chip capacitor	[1] 1.8 pF
C4, C10	multilayer ceramic chip capacitor	[2] 20 nF
C5	multilayer ceramic chip capacitor	[3] 33 pF
C6	multilayer ceramic chip capacitor	[1] 5.6 pF
C7	multilayer ceramic chip capacitor	[3] 6.2 pF
C9	tekelec trimmer; type 37283	0.4 to 2.5 pF
C11	multilayer ceramic chip capacitor	[1] 33 pF
R1	SMD resistor	2.2 $\Omega$ (2 in parallel)
R2	SMD resistor	22 $\Omega$

[1] American Technical Ceramics type 100A or capacitor of same quality.

[2] American Technical Ceramics type 200B or capacitor of same quality.

[3] American Technical Ceramics type 100B or capacitor of same quality.

9. Package outline

Ceramic surface-mounted package; 2 leads

SOT538A




Fig 6. Package outline SOT538A

## 10. Revision history

Table 10. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
BLA1011-2 v.6	20130506	Product data sheet	-	BLA1011-2 v.5
Modifications:		<ul style="list-style-type: none"><li>• The format of this data sheet has been redesigned to comply with the new identity guidelines of NXP Semiconductors.</li><li>• Legal texts have been adapted to the new company name where appropriate.</li><li>• Package outline drawings have been updated to the latest version.</li></ul>		
BLA1011-2 v.5	20031119	Product specification	-	BLA1011-2 v.4

## 11. Legal information

### 11.1 Data sheet status

Document status <sup>[1][2]</sup>	Product status <sup>[3]</sup>	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <http://www.nxp.com>.

### 11.2 Definitions

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

**Short data sheet** — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

### 11.3 Disclaimers

**Limited warranty and liability** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

**Right to make changes** — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use** — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

**Limiting values** — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

**Terms and conditions of commercial sale** — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nxp.com/profile/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

**No offer to sell or license** — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.



**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

**Non-automotive qualified products** — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond

NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

## 11.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

## 12. Contact information

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: [salesaddresses@nxp.com](mailto:salesaddresses@nxp.com)

**13. Contents**

**1 Product profile . . . . . 1**

1.1 General description . . . . . 1

1.2 Features and benefits . . . . . 1

1.3 Applications . . . . . 1

**2 Pinning information . . . . . 1**

**3 Ordering information . . . . . 2**

**4 Limiting values . . . . . 2**

**5 Thermal characteristics . . . . . 2**

**6 Characteristics . . . . . 2**

**7 Application information . . . . . 3**

7.1 Ruggedness in class-AB operation . . . . . 3

**8 Test information . . . . . 5**

**9 Package outline . . . . . 6**

**10 Revision history . . . . . 7**

**11 Legal information . . . . . 8**

11.1 Data sheet status . . . . . 8

11.2 Definitions . . . . . 8

11.3 Disclaimers . . . . . 8

11.4 Trademarks . . . . . 9

**12 Contact information . . . . . 9**

**13 Contents . . . . . 10**

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.