

### 500V N-Channel Power MOSFET



TO-220

**ITO-220** 



Pin Definition:

- Gate
  Drain
- 3. Source

#### PRODUCT SUMMARY

V <sub>DS</sub> (V)	$R_{DS(on)}(\Omega)$	I <sub>D</sub> (A)
500	0.44 @ V <sub>GS</sub> =10V	14

#### **General Description**

The TSM15N50 N-Channel enhancement mode Power MOSFET is produced by planar stripe DMOS technology. This advanced technology has been especially tailored to minimize on-state resistance, provide superior switching performance, and withstand high energy pulse in the avalanche and commutation mode. These devices are well suited for high efficiency switch mode power supply, electronic lamp ballast based on half bridge.

#### **Features**


- Low R<sub>DS(ON)</sub> 0.44Ω (Max.)
- Low gate charge typical @ 39nC (Typ.)
- Improve dv/dt capability

#### **Ordering Information**

Part No.	Package	Packing
TSM15N50CZ C0	TO-220	50pcs / Tube
TSM15N50CZ C0G	TO-220	50pcs / Tube
TSM15N50CI C0	ITO-220	50pcs / Tube
TSM15N50CI C0G	ITO-220	50pcs / Tube

Note: "G" denotes Halogen Free Product.

#### Block Diagram



N-Channel MOSFET

#### Absolute Maximum Rating (Ta = 25°C unless otherwise noted)

Parameter	Symbol	Limit	Unit
Drain-Source Voltage	V <sub>DS</sub>	500	V
Gate-Source Voltage	$V_{GS}$	±30	V
Continuous Drain Current(T <sub>C</sub> =25°C)	I <sub>D</sub>	14	А
Pulsed Drain Current *	I <sub>DM</sub>	56	А
Peak Diode Recovery dv/dt (Note 3)	dv/dt	4.5	V/ns
Single Pulse Avalanche Energy (Note 2)	E <sub>AS</sub>	630	mJ
Avalanche Current (Repetitive) (Note 1)	I <sub>AR</sub>	14	Α
Repetitive Avalanche Energy (Note 1)	E <sub>AR</sub>	23.1	mJ
Operating Junction Temperature	TJ	150	°C
Storage Temperature Range	T <sub>STG</sub>	-55 to +150	°C

<sup>\*</sup> Limited by maximum junction temperature



### 500V N-Channel Power MOSFET



#### **Thermal Performance**

Parameter	Symbol	TO-220	ITO-220	Unit
Thermal Resistance - Junction to Case	R⊖ <sub>JC</sub>	0.54 2.34		0000
Thermal Resistance - Junction to Ambient	RΘ <sub>JA</sub>	62.5		°C/W

Notes: Surface mounted on FR4 board t ≤ 10sec

**Electrical Specifications** (Tc = 25°C unless otherwise noted)

Parameter	Conditions	Symbol	Min	Тур	Max	Unit
Static						
Drain-Source Breakdown Voltage	$V_{GS} = 0V, I_D = 250uA$	BV <sub>DSS</sub>	500	7-	1	V
Drain-Source On-State Resistance	$V_{GS} = 10V, I_D = 7.0A$	R <sub>DS(ON)</sub>		0.35	0.44	Ω
Gate Threshold Voltage	$V_{DS} = V_{GS}, I_{D} = 250uA$	V <sub>GS(TH)</sub>	2.0	<b>V</b>	4.0	V
Zero Gate Voltage Drain Current	$V_{DS} = 500V, V_{GS} = 0V$	I <sub>DSS</sub>			1	uA
Gate Body Leakage	$V_{GS} = \pm 30V, V_{DS} = 0V$	I <sub>GSS</sub>	2		±100	nA
Forward Transconductance	$V_{DS} = 30V, I_{D} = 7.0A$	g <sub>fs</sub>		10		S
Diode Forward Voltage	$I_{S} = 14A, V_{GS} = 0V$	$V_{SD}$			1.5	V
Dynamic <sup>b</sup>						
Total Gate Charge	V 400V I 44A	$Q_g$		39		
Gate-Source Charge	$V_{DS} = 400V, I_{D} = 14A,$ $V_{GS} = 10V$	$Q_gs$		11		nC
Gate-Drain Charge	V <sub>GS</sub> = 10V	$Q_{gd}$		8.6		
Input Capacitance	$V_{DS} = 25V, V_{GS} = 0V,$	C <sub>iss</sub>		2263		
Output Capacitance	$V_{DS} = 25V, V_{GS} = 0V,$ f = 1.0MHz	C <sub>oss</sub>		211		pF
Reverse Transfer Capacitance	1 = 1.0WH12	$C_{rss}$		6.4		
Switching <sup>c</sup>						
Turn-On Delay Time		t <sub>d(on)</sub>		65		
Turn-On Rise Time	$V_{DD} = 250V, I_D = 14A,$	t <sub>r</sub>		55		
Turn-Off Delay Time	$R_G = 25\Omega$	t <sub>d(off)</sub>		144		nS
Turn-Off Fall Time		t <sub>f</sub>		58		
Reverse Recovery Time	$V_{GS} = 0V, I_S = 14A,$	t <sub>fr</sub>		381		nS
Reverse Recovery Charge	$dI_F/dt = 100A/us$	$Q_{fr}$		4.4		uC

#### Notes:


- 1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
- 2. Max Rating  $E_{AS}$  Test Condition:  $V_{DD}$  = 50V,  $I_{AS}$ =14A, L=5.9mH,  $R_{G}$ =25 $\Omega$ , Starting  $T_{J}$ =25 $^{\circ}$ C
- 3. Guaranteed 100% E<sub>AS</sub> Test Condition:  $V_{DD}$  = 50V,  $I_{AS}$ =14A, L=1mH,  $R_{G}$ =25 $\Omega$ , Starting  $T_{J}$ =25 $^{\circ}$ C
- 4.  $I_{SD} \le 14A$ , di/dt  $\le 200A/uS$ ,  $V_{DD} \le BV$ , Starting  $T_J = 25^{\circ}C$
- 5. Pulse test: pulse width ≤300uS, duty cycle ≤2%
- 6. b For design reference only, not subject to production testing.
- 7. c Switching time is essentially independent of operating temperature.



### 500V N-Channel Power MOSFET



**Electrical Characteristics Curve** (Tc = 25°C, unless otherwise noted)







### 500V N-Channel Power MOSFET





#### **Electrical Characteristics Curve** (Ta = 25°C, unless otherwise noted)




BV<sub>DSS</sub> vs. Junction Temperature








Capacitance vs. Drain-Source Voltage



### Maximum Safe Operating Area (ITO-220)



Version: D1702

4/10




# 500V N-Channel Power MOSFET




**Electrical Characteristics Curve** (Ta = 25°C, unless otherwise noted)

#### Normalized Thermal Transient Impedance, Junction-to-Ambient



### Normalized Thermal Transient Impedance, Junction-to-Ambient(ITO-220)







### 500V N-Channel Power MOSFET



### **Gate Charge Test Circuit & Waveform**




### **E<sub>AS</sub> Test Circuit & Waveform**



### 500V N-Channel Power MOSFET



### **Diode Reverse Recovery Time Test Circuit & Waveform**






### 500V N-Channel Power MOSFET




### **TO-220 Mechanical Drawing**



Unit: Millimeters

#### **MARKING DIAGRAM**






### 500V N-Channel Power MOSFET




### **ITO-220 Mechanical Drawing**



**Unit: Millimeters** 

#### **MARKING DIAGRAM**



= Halogen Free


= Year Code

**WW** = Week Code  $(01\sim52)$ 

Factory Code



500V N-Channel Power MOSFET



Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.