


PME271E610MR30

Aliases (P277CP104M300A)

Obsolete

PME271E/P277, Film, Metallized Paper, Safety, 0.1 uF, 20%, 300 VAC (X1), 630 VDC, 110°C, Lead Spacing = 20.3mm



Click [here](#) for the 3D model.

Dimensions	
L	24mm MAX
H	16.5mm MAX
T	11.3mm MAX
S	20.3mm +/-0.4mm
LL	30mm +5mm
F	0.8mm +/-0.05mm

Packaging Specifications	
Packaging	Bulk, Bag
Packaging Quantity	150

General Information	
Series	PME271E/P277
Dielectric	Metallized Paper
Style	Radial
Features	EMI Safety
RoHS	Yes
Lead	Wire Leads
Safety Class	X1
Qualifications	ENEC, UL, cUL
AEC-Q200	No
THB Performance	No
Construction	Molded
Typical Component Weight	6.3 g
Miscellaneous	SRF= 4.1 MHz.

Specifications	
Capacitance	0.1 uF
Capacitance Tolerance	20%
Voltage AC	300 VAC (X1)
Voltage DC	630 VDC
Temperature Range	-40/+110°C
Rated Temperature	110°C
Dissipation Factor	1.3% 1kHz
Insulation Resistance	12 GOhms
Max dV/dt	600 V/us

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.