HARRIS

IRF640/641/642/643
IRF640R/641R/642R/643R

N-Channel Power MOSFETs
Avalanche Energy Rated*

August 1991

Features

- 16A and 18A, 150V - 200V
- $r_{DS}(on)$ = 0.18Ω and 0.22Ω
- Single Pulse Avalanche Energy Rated*
- SOA is Power-Dissipation Limited
- Nanosecond Switching Speeds
- Linear Transfer Characteristics
- High Input Impedance

Description

The IRF640, IRF641, IRF642, and IRF643 are n-channel enhancement-mode silicon-gate power field-effect transistors. IRF640R, IRF641R, IRF642R and IRF643R types are advanced power MOSFETs designed, tested, and guaranteed to withstand a specified level of energy in the breakdown avalanche mode of operation. All of these power MOSFETs are designed for applications such as switching regulators, switching converters, motor drivers, relay drivers, and drivers for high-power bipolar switching transistors requiring high speed and low gate-drive power. These types can be operated directly from integrated circuits.

The IRF types are supplied in the JEDEC TO-220AB plastic package.

Package

TO-220AB
TOP VIEW



Terminal Diagram

N-CHANNEL ENHANCEMENT MODE



Absolute Maximum Ratings (T_C = +25°C), Unless Otherwise Specified

	IRF640 IRF640R	IRF641 IRF641R	IRF642 IRF642R	IRF643 IRF643R	UNITS
Drain-Source Voltage (1) ..... V_{DS}	200	150	200	150	V
Drain-Gate Voltage (R_{GS} = 20kΩ) (1) ..... V_{DGR}	200	150	200	150	V
Continuous Drain Current					
T_C = +25°C ..... I_D	18	18	16	16	A
T_C = +100°C ..... I_D	11	11	10	10	A
Pulsed Drain Current (3) ..... I_{DM}	72	72	64	64	A
Gate-Source Voltage ..... V_{GS}	±20	±20	±20	±20	V
Maximum Power Dissipation					
T_C = +25°C ..... P_D	125	125	125	125	W
Linear Derating Factor	1.0	1.0	1.0	1.0	W/°C
Inductive Current, Clamped ..... I_{LM} (See Figure 14, L = 100μH)	72	72	64	64	A
Single Pulse Avalanche Energy Rating (4) ..... E_{AS}*	580	580	580	580	mJ
Operating and Storage Junction ..... T_J, T_{STG} Temperature Range	-55 to +150	-55 to +150	-55 to +150	-55 to +150	°C
Maximum Lead Temperature for Soldering ..... T_L (0.063" (1.6mm) from case for 10s)	300	300	300	300	°C

NOTES:

1. T_J = +25°C to +150°C.
2. Pulse Test: Pulse width ≤ 300μs, Duty Cycle ≤ 2%.
3. Repetitive rating: Pulse width limited by maximum junction temperature. See Transient Thermal Impedance Curve (Figure 5).
4. V_{DD} = 50V, starting T_J = +25°C, L = 2.7mH, R_{GS} = 25Ω, I_{PEAK} = 18A. See Figure 15.

*R Suffix Types Only

CAUTION: These devices are sensitive to electrostatic discharge. Proper I.C. handling procedures should be followed.

File Number **1585.1**

Electrical Characteristics T_C = 25°C, Unless Otherwise Specified

CHARACTERISTIC	SYMBOL	TEST CONDITIONS	LIMITS MIN	LIMITS TYP	LIMITS MAX	UNITS
Drain-Source Breakdown Voltage IRF640/642, IRF640R/642R	BV_{DSS}	V_{GS} = 0V, I_D = 250µA	200	-	-	V
IRF641/643, IRF641R/643R			150	-	-	V
Gate Threshold Voltage	$V_{GS(TH)}$	V_{DS} = V_{GS}, I_D = 250µA	2.0	-	4.0	V
Gate-Source Leakage Forward	I_{GSS}	V_{GS} = 20V	-	-	500	nA
Gate-Source Leakage Reverse	I_{GSS}	V_{GS} = -20V	-	-	-500	nA
Zero Gate Voltage Drain Current	I_{DSS}	V_{DS} = Max Rating, V_{GS} = 0V	-	-	250	µA
		V_{DS} = Max Rating x 0.8, V_{GS} = 0V, T_J = +125°C	-	-	1000	µA
On-State Drain Current (Note 2) IRF640/641, IRF640R/641R	$I_{D(ON)}$	V_{DS} > $I_{D(ON)}$ x $r_{DS(ON)\ Max}$, V_{GS} = 10V	18	-	-	A
IRF642/643, IRF642R/643R			16	-	-	A
Static Drain-Source On-State Resistance (Note 2) IRF640/641, IRF640R/641R	$r_{DS(ON)}$	V_{GS} = 10V, I_D = 10A	-	0.14	0.18	Ω
IRF642/643, IRF642R/643R			-	0.20	0.22	Ω
Forward Transconductance (Note 2)	g_{fs}	$V_{DS} \geq$ 50V, I_D = 10A	6.7	10	-	S(℧)
Input Capacitance	C_{ISS}	V_{GS} = 0V, V_{DS} = 25V, f = 1.0MHz See Figure 10	-	1275	-	pF
Output Capacitance	C_{OSS}		-	400	-	pF
Reverse Transfer Capacitance	C_{RSS}		-	100	-	pF
Turn-On Delay Time	$t_{d(ON)}$	V_{DD} = 100V, I_D = 18A, R_G = 9.1Ω See Figure 16. (MOSFET switching times are essentially independent of operating temperature)	-	13	21	ns
Rise Time	t_r		-	50	77	ns
Turn-Off Delay Time	$t_{d(OFF)}$		-	46	68	ns
Fall Time	t_f		-	35	54	ns
Total Gate Charge (Gate-Source + Gate-Drain)	Q_g	V_{GS} = 10V, I_D = 18A, V_{DS} = 0.8V Max Rating. See Figure 17 for test circuit. (Gate charge is essentially independent of operating temperature.)	-	43	64	nC
Gate-Source Charge	Q_{gs}		-	8	-	nC
Gate-Drain ("Miller") Charge	Q_{gd}		-	22	-	nC
Internal Drain Inductance	L_D	Measured from the contact screw on tab to center of die. Modified MOSFET symbol showing the internal device inductances.	-	3.5	-	nH
		Measured from the drain lead, 6mm (0.25in.) from package to center of die	-	4.5	-	nH
Internal Source Inductance	L_S	Measured from the source lead, 6mm (0.25") from header and source bonding pad.	-	7.5	-	nH
Junction-to-Case	$R_{\theta JC}$		-	-	1.0	°C/W
Case-to-Sink	$R_{\theta CS}$	Mounting surface flat, smooth and greased	-	0.5	-	°C/W
Junction-to-Ambient	$R_{\theta JA}$	Free air operation	-	-	80	°C/W



Source Drain Diode Ratings and Characteristics

Continuous Source Current (Body Diode)	I_S	Modified MOSFET symbol showing the integral reverse P-N junc. rectifier.	-	-	18	A
Pulse Source Current (Body Diode) (Note 3)	I_{SM}		-	-	72	A
Diode Forward Voltage (Note 2)	V_{SD}	T_J = +25°C, I_S = 18A, V_{GS} = 0V	-	-	2.0	V
Reverse Recovery Time	t_{rr}	T_J = +25°C, I_F = 18A, dI_F/dt = 100A/µs	120	240	530	ns
Reverse Recovered Charge	Q_{RR}	T_J = +150°C, I_F = 18A, dI_F/dt = 100A/µs	1.3	2.8	5.6	µC
Forward Turn-on Time	t_{ON}	Intrinsic turn-on time is negligible. Turn-on speed is substantially controlled by L_S + L_D.	-	-	-	-



NOTES: 1. T_J = +25°C to +150°C
2. Pulse Test: Pulse width ≤ 300µs, Duty Cycle ≤ 2%
3. Repetitive Rating: Pulse width limited by max. junction temperature. See Transient Thermal Impedance Curve (Figure 5)
4. V_{DD} = 20V, Start T_J = +25°C, L = 3.37mH, R_{GS} = 25Ω, I_{PEAK} = 18A (See Figure 15)

Performance Curves



FIGURE 1. TYPICAL OUTPUT CHARACTERISTICS



FIGURE 2. TYPICAL TRANSFER CHARACTERISTICS



FIGURE 3. TYPICAL SATURATION CHARACTERISTICS



FIGURE 4. MAXIMUM SAFE OPERATING AREA



FIGURE 5. MAXIMUM EFFECTIVE TRANSIENT THERMAL IMPEDANCE, JUNCTION-TO-CASE vs PULSE DURATION

Performance Curves (Continued)



FIGURE 6. TYPICAL TRANSCONDUCTANCE vs DRAIN CURRENT



FIGURE 7. TYPICAL SOURCE-DRAIN DIODE FORWARD VOLTAGE



FIGURE 8. BREAKDOWN VOLTAGE vs TEMPERATURE



FIGURE 9. NORMALIZED ON-RESISTANCE vs TEMPERATURE



FIGURE 10. TYPICAL CAPACITANCE vs DRAIN-TO-SOURCE VOLTAGE



FIGURE 11. TYPICAL GATE CHARGE vs GATE-TO-SOURCE VOLTAGE

Performance Curves (Continued)



FIGURE 12. TYPICAL ON-RESISTANCE VS. DRAIN CURRENT



FIGURE 13. MAXIMUM DRAIN CURRENT VS. CASE TEMPERATURE



FIGURE 14a. CLAMPED INDUCTIVE TEST CIRCUIT



FIGURE 15a. UNCLAMPED ENERGY TEST CIRCUIT



FIGURE 14b. CLAMPED INDUCTIVE WAVEFORMS



FIGURE 15b. UNCLAMPED ENERGY WAVEFORMS



FIGURE 16. SWITCHING TIME TEST CIRCUIT



FIGURE 17. GATE CHARGE TEST CIRCUIT