Technical Data Sheet



SP6T Ramses SMA 18GHz Latching Self-cut-off Indicators 28Vdc

TTL Diodes Pins Terminals

PAGE 1/2 ISSUE 22-03-22 SERIE : SPnT PART NUMBER : R573453620

RF CHARACTERISTICS

Number of ways : 6

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18
VSWR max	1.20	1.30	1.40	1.50
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB
Isolation min	80 dB	70 dB	60 dB	60 dB
Average power (*)	240 W	150 W	120 W	100 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING

Nominal current ** : 125 mA / RESET : 750 mA ****

Actuator voltage (Vcc) : 28V (24 to 30V)

Terminals : solder pins (250°C max. / 30 sec.)

TTL inputs (E) - High level : 2.2 to 5.5 V / 800μA at 5.5 V - Low level : 0 to 0.8 V / 20μA at 0.8 V

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012
Life : 5 million cycles per position

Switching Time*** : <15 ms

Construction : Splashproof

Weight : < 220 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)

(**** Reset : supply voltage time 1sec. max. / duty cycle 10%)









SP6T Ramses SMA 18GHz Latching Self-cut-off Indicators 28Vdc TTL Diodes Pins Terminals

PAGE 2/2 ISSUE 22-03-22 SERIE : SPnT PART NUMBER : R573453620

DRAWING




RF Continuity	Ind.
All ports open	
$IN \leftrightarrow 1$	D.E
$IN \leftrightarrow 2$	D.F
$IN \leftrightarrow 3$	D.G
$IN \leftrightarrow 4$	D.H
$IN \leftrightarrow 5$	D.I
IN ↔ 6	D.J
	All ports open $IN \leftrightarrow 1$ $IN \leftrightarrow 2$ $IN \leftrightarrow 3$ $IN \leftrightarrow 4$ $IN \leftrightarrow 5$




General tolerances: ±0,5 mm [0,02 in]

LABEL





SCHEMATIC DIAGRAM



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.