

IRFP244, IRFP245 IRFP246, IRFP247

**N-Channel Power MOSFETs
Avalanche Energy Rated**

August 1991

Features


- 15A and 14A, 275V - 250V
- $r_{DS(on)} = 0.28\Omega$ and 0.34Ω
- Single Pulse Avalanche Energy Rated
- SOA is Power-Dissipation Limited
- Nanosecond Switching Speeds
- Linear Transfer Characteristics
- High Input Impedance
- 275V, 250V DC Rated - 120V AC Line System Operation

Description

The IRFP244, IRFP245, IRFP246, and IRFP247 are advanced power MOSFETs designed, tested and guaranteed to withstand a specified level of energy in the breakdown avalanche mode of operation. These are n-channel enhancement-mode silicon-gate power field-effect transistors designed for applications such as switching regulators, switching converters, motor drivers, relay drivers, and drivers for high-power bipolar switching transistors requiring high speed and low gate-drive power. These types can be operated directly from integrated circuits.


The IRFP types are supplied in the JEDEC TO-247 plastic package.

Package



Terminal Diagram

N-CHANNEL ENHANCEMENT MODE



4

N-CHANNEL
POWER MOSFETS

Absolute Maximum Ratings ($T_C = +25^\circ C$), Unless Otherwise Specified


	IRFP244	IRFP245	IRFP246	IRFP247	UNITS
Drain-Source Voltage (1)	V_{DS}	250	250	275	V
Drain-Gate Voltage ($R_{GS} = 20k\Omega$) (1)	V_{DGR}	250	250	275	V
Continuous Drain Current					
$T_C = +25^\circ C$	I_D	15	14	15	A
$T_C = +100^\circ C$	I_D	9.7	8.8	9.7	A
Pulsed Drain Current (3)	I_{DM}	60	56	60	A
Gate-Source Voltage	V_{GS}	± 20	± 20	± 20	V
Maximum Power Dissipation					
$T_C = +25^\circ C$	P_D	150	150	150	W
Linear Derating Factor		1.2	1.2	1.2	W/ $^\circ C$
Single Pulse Avalanche Energy Rating (4)	E_{as}	550	550	550	mJ
Operating and Storage Junction	T_J, T_{STG}	-55 to +150	-55 to +150	-55 to +150	$^\circ C$
Temperature Range					
Maximum Lead Temperature for Soldering (0.063" (1.6mm) from case for 10s)	T_L	300	300	300	$^\circ C$

NOTES:

1. $T_J = +25^\circ C$ to $+150^\circ C$.
2. Pulse Test: Pulse width $\leq 300\mu s$, Duty Cycle $\leq 2\%$.
3. Repetitive Rating: Pulse width limited by max. junction temperature. See Transient Thermal Impedance Curve (Figure 5).
4. $V_{DD} = 50V$, starting $T_J = +25^\circ C$, $L = 4.0mH$, $R_{GS} = 25\Omega$, $I_{PEAK} = 15A$. See Figures 14 and 15.

Specifications IRFP244, IRFP245, IRFP246, IRFP247

Electrical Characteristics $T_C = +25^\circ\text{C}$, Unless Otherwise Specified

CHARACTERISTIC	SYMBOL	TEST CONDITIONS	LIMITS			UNITS
			MIN	TYP	MAX	
Drain-Source Breakdown Voltage IRFP244, IRFP245	BV_{DSS}	$V_{\text{GS}} = 0\text{V}, I_D = 250\mu\text{A}$	250	-	-	V
IRFP246, IRFP247			275	-	-	V
Gate Threshold Voltage	$V_{\text{GS}(\text{TH})}$	$V_{\text{DS}} = V_{\text{GS}}, I_D = 250\mu\text{A}$	2.0	-	4.0	V
Gate-Source Leakage Forward	I_{GSS}	$V_{\text{GS}} = 20\text{V}$	-	-	500	nA
Gate-Source Leakage Reverse	I_{GSS}	$V_{\text{GS}} = -20\text{V}$	-	-	-500	nA
Zero Gate Voltage Drain Current	I_{DSS}	$V_{\text{DS}} = \text{Max Rating}, V_{\text{GS}} = 0\text{V}$	-	-	250	μA
		$V_{\text{DS}} = \text{Max Rating} \times 0.8, V_{\text{GS}} = 0\text{V}, T_C = +125^\circ\text{C}$	-	-	1000	μA
On-State Drain Current (Note 2) IRFP244, IRFP246	$I_{\text{D}(\text{ON})}$	$V_{\text{DS}} > I_{\text{D}(\text{ON})} \times t_{\text{DS}(\text{ON})} \text{ Max}, V_{\text{GS}} = 10\text{V}$	15	-	-	A
IRFP245, IRFP247			14	-	-	A
Static Drain-Source On-State Resistance (Note 2) IRFP244, IRFP246	$r_{\text{DS}(\text{ON})}$	$V_{\text{GS}} = 10\text{V}, I_D = 10\text{A}$	-	0.20	0.28	Ω
IRFP245, IRFP247			-	0.24	0.34	V
Forward Transconductance (Note 2)	g_{fs}	$V_{\text{DS}} \geq 50\text{V}, I_D = 10\text{A}$	6.7	11	-	$S(\text{f})$
Input Capacitance	C_{ISS}	$V_{\text{GS}} = 0\text{V}, V_{\text{DS}} = 25\text{V}, f = 1.0\text{MHz}$	-	1300	-	pF
Output Capacitance	C_{OSS}	See Figure 10	-	320	-	pF
Reverse Transfer Capacitance	C_{RSS}	-	-	69	-	pF
Turn-On Delay Time	$t_{\text{d}(\text{ON})}$	$V_{\text{DD}} = 125\text{V}, I_D = 15\text{A}, R_G = 9.1\Omega$, See Figure 16. (MOSFET switching times are essentially independent of operating temperature)	-	16	24	ns
Rise Time	t_r	-	-	67	100	ns
Turn-Off Delay Time	$t_{\text{d}(\text{OFF})}$	-	-	53	80	ns
Fall Time	t_f	-	-	49	74	ns
Total Gate Charge (Gate-Source + Gate-Drain)	Q_g	$V_{\text{GS}} = 10\text{V}, I_D = 15\text{A}, V_{\text{DS}} = 0.8 \text{ Max}$ Rating. See Figure 17 for test circuit.	-	39	59	nC
Gate-Source Charge	Q_{gs}	(Gate charge is essentially independent of operating temperature.)	-	6.6	-	nC
Gate-Drain ("Miller") Charge	Q_{gd}	-	-	20	-	nC
Internal Drain Inductance	L_D	Measured from the drain lead, 6mm (0.25") from package to center of die.	Modified MOSFET symbol showing the internal device inductances. 	-	5.0	nH
Internal Source Inductance	L_S	Measured from the source lead, 6mm (0.25") from package to source bonding pad.		-	12.5	nH
Junction-to-Case	$R_{\theta\text{JC}}$	-	-	-	0.83	$^\circ\text{C}/\text{W}$
Case-to-Sink	$R_{\theta\text{CS}}$	Mounting surface flat, smooth and greased	-	0.1	-	$^\circ\text{C}/\text{W}$
Junction-to-Ambient	$R_{\theta\text{JA}}$	Free air operation	-	-	30	$^\circ\text{C}/\text{W}$

Source Drain Diode Ratings and Characteristics

Continuous Source Current (Body Diode)	I_S	Modified MOSFET symbol showing the integral reverse P-N junc. rectifier.	-	-	15	A
Pulse Source Current (Body Diode) (Note 3)	I_{SM}		-	-	60	A
Diode Forward Voltage (Note 2)	V_{SD}	$T_J = +25^\circ\text{C}, I_S = 15\text{A}, V_{\text{GS}} = 0\text{V}$	-	-	1.8	V
Reverse Recovery Time	t_{rr}	$T_J = +25^\circ\text{C}, I_F = 14\text{A}, dI/dt = 100\text{A}/\mu\text{s}$	150	300	640	ns
Reverse Recovered Charge	Q_{RR}	$T_J = +25^\circ\text{C}, I_F = 14\text{A}, dI/dt = 100\text{A}/\mu\text{s}$	1.6	3.4	7.2	μC
Forward Turn-on Time	t_{ON}	Intrinsic turn-on time is negligible. Turn-on speed is substantially controlled by $L_S + L_D$.	-	-	-	-

NOTES: 1. $T_J = +25^\circ\text{C}$ to $+150^\circ\text{C}$
2. Pulse Test: Pulse width $\leq 300\mu\text{s}$,
Duty Cycle $\leq 2\%$

3. Repetitive Rating: Pulse width limited by max.
junction temperature. See Transient Thermal
Impedance Curve (Figure 5)

4. $V_{\text{DD}} = 50\text{V}$, Start $T_J = +25^\circ\text{C}$, $L = 4.0\text{mH}$,
 $R_{\text{GS}} = 25\Omega$, $I_{\text{PEAK}} = 15\text{A}$.
(See Figures 14 & 15)

IRFP244, IRFP245, IRFP246, IRFP247

4

N-CHANNEL
POWER MOSFETs




Fig. 1 - Typical output characteristics.




Fig. 2 - Typical transfer characteristics.




Fig. 3 - Typical saturation characteristics.




Fig. 4 - Maximum safe operating area.




Fig. 5 - Maximum effective transient thermal impedance, junction-to-case vs. pulse duration.

IRFP244, IRFP245, IRFP246, IRFP247




Fig. 6 - Typical transconductance vs. drain current.




Fig. 7 - Typical source-drain diode forward voltage.




Fig. 8 - Breakdown voltage vs. temperature.




Fig. 9 - Normalized on-resistance vs. temperature.




Fig. 10 - Typical capacitance vs. drain-to-source voltage.




Fig. 11 - Typical gate charge vs. gate-to-source voltage.




Fig. 12 – Typical on-resistance vs. drain current.




Fig. 13 – Maximum drain current vs case temperature.




Fig. 14 – Unclamped energy test circuit.




Fig. 15 – Unclamped energy waveforms.




Fig. 16 – Switching time test circuit.




Fig. 17 – Gate charge test circuit.