Technical Data Sheet



DPDT Ramses N 12.4GHz Latching Self-cut-off Indicators 28Vdc

Diodes Pins Terminals

PAGE 1/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577163002

RF CHARACTERISTICS

Frequency range : 0 - 12.4 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 1	1 - 2	2 - 3	3 - 8	8 - 12.4
VSWR max	1.15	1.20	1.25	1.35	1.50
Insertion loss max	0.15 dB	0.20 dB	0.25 dB	0.35 dB	0.50 dB
Isolation min	85 dB	80 dB	75 dB	70 dB	60 dB
Average power (*)	700 W	500 W	400 W	250 W	200 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING
Nominal current ** : 125 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / NEGATIVE COMMON
Terminals : solder pins (250°C max. / 30 sec.)

Indicator rating : 1 W / 30 V / 100 mA
Self cut-off time : 40 ms < CT < 120 ms

MECHANICAL CHARACTERISTICS

Connectors : N female per MIL-C 39012

Life : 2.5 million cycles

Switching Time*** : < 15 msConstruction : Splashproof
Weight : < 215 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)







DPDT Ramses N 12.4GHz Latching Self-cut-off Indicators 28Vdc

Diodes Pins Terminals


PAGE **2/2**


ISSUE **22-03-22**


SERIE: DPDT

PART NUMBER: **R577163002**

DRAWING








General tolerances: ±0,5 mm [0,02 in]

SCHEMATIC DIAGRAM





LABEL

+1 +2 -C 1 2 °C **RADIALL®** R577163002 0 - 12.4 GHz Un: 28V Lot : _ _ _ _

Voltage RF Continuity Ind. -C +1 $1 \leftrightarrow 2 / 3 \leftrightarrow 4$ -C +2