Technical Data Sheet



SP5T Terminated Ramses SMA2.9 40GHz Latching Self-cut-off Indicators 28Vdc Diodes D-sub connector

PAGE 1/2 ISSUE 30.01.15 SERIE : SPnT PART NUMBER : R574853505

RF CHARACTERISTICS

Number of ways : 5

Frequency range : 0 - 40 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 6	6 - 12.4	12.4 - 18	18 - 26.5	26.5 - 40
VSWR max	1.30	1.40	1.50	1.70	2.20
Insertion loss max	0.20 dB	0.40 dB	0.50 dB	0.70 dB	1.10 dB
Isolation min	70 dB	60 dB	60 dB	55 dB	50 dB
Average power (*)	40 W	30 W	25 W	15 W	5 W

TERMINATION IMPEDANCE : 50 Ohms

TERM. AVG. POWER AT 25° C : 1 W per termination / 3 W total power

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING

Nominal current ** : 125 mA / RESET : 625 mA ****

Actuator voltage (Vcc) : 28V (24 to 30V) / NEGATIVE COMMON

Terminals : 25 pins D-SUB male connector

 $\begin{array}{ll} \text{Indicator rating} & : \ 1 \ \text{W} \ / \ 30 \ \text{V} \ / \ 100 \ \text{mA} \\ \text{Self cut-off time} & : \ 40 \ \text{ms} < \text{CT} < 120 \ \text{ms} \end{array}$

MECHANICAL CHARACTERISTICS

Connectors : SMA 2.9 female per MIL-C 39012
Life : 2.000.000 cycles per position

Switching Time*** : < 15 msConstruction : Splashproof
Weight : < 250 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)

(**** Reset : supply voltage time 1sec. max. / duty cycle 10%)




Technical Data Sheet





SP5T Terminated Ramses SMA2.9 40GHz Latching Self-cut-off Indicators 28Vdc Diodes D-sub connector

PAGE 2/2 ISSUE 30.01.15 SERIE : SPNT PART NUMBER : R574853505



Voltage	RF Continuity	Ind.
-C +RESET	All ports open	
-C +1	$IN \leftrightarrow 1$	D.G
-C +2	$IN \leftrightarrow 2$	D.H
-C +3	$IN \leftrightarrow 3$	D.I
-C +5	$IN \leftrightarrow 5$	D.E
-C +6	$IN \leftrightarrow 6$	D.F






RADIALL® R574853505 0 - 40 GHz Un : 28V Lot : _ _ _



General tolerances : ±0.5 mm

SCHEMATIC DIAGRAM



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.