



SPDT Terminated Ramses SMA 3GHz Latching Self-cut-off Indicators 28Vdc Positive common Diodes Internal loads Pins terminals

PAGE 1/2 ISSUE 09-03-21 SERIE : SPDT ZC PART NUMBER : R585363210

RF CHARACTERISTICS

Frequency range : 0 - 3 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3
VSWR max	1.20
Insertion loss max	0.20 dB
Isolation min	80 dB
Average power (*)	240 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING
Nominal current ** : 160 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / POSITIVE COMMON
Terminals : solder pins (250°C max. / 30 sec.)
Indicator rating : 1 W / 30 V / 100 mA

Indicator rating : 1 W / 30 V / 100 mA
Self cut-off time : 40 ms < CT < 120 ms

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 2 million cycles
Switching Time*** : < 10 ms
Construction : Splashproof

Weight : **< 100 g**

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)







 50Ω Termination

SPDT Terminated Ramses SMA 3GHz Latching Self-cut-off Indicators 28Vdc Positive common Diodes Internal loads Pins terminals

PAGE **2/2** ISSUE **09-03-21** SERIE: SPDT ZC PART NUMBER: **R585363210 DRAWING** 2.189 55.6 0 0.44 0.44 11.18 11.18 [0.138 min.] LABEL 3.5 min. -2 2 +C 0 - 3 GHz Un: 28V **RADIALL®** R585363210 Lot : _ _ _ _ [0.122][0.094]С 4 x ¯ Ø 3.1 [0.059 max.] 1.5 max. [0.303 max.] 7.7 max. [0.441] 11.2 [1.321] 33.55 **@@@ %** 00 0 General tolerances: ±0,5 mm [0,02 in] **SCHEMATIC DIAGRAM** Indicator terminals RF input -02 50Ω Termination Actuator RF Continuity Voltage Ind. ¥₩0-С +C C↔1 / 2↔50Ω +C -2 $C\leftrightarrow 2/1\leftrightarrow 50\Omega$ CUT OFF Power input ∞ terminals ₹W0-0