



DPDT Ramses SMA2.9 40GHz Latching Self-cut-off Indicators 12Vdc
Positive common Diodes D-sub connector

PAGE 1/2 ISSUE 06-02-18 SERIE : DPDT PART NUMBER : R577862017

RF CHARACTERISTICS

Frequency range : 0 - 40 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 6	6 - 12.4	12.4 - 18	18 - 26.5	26.5 - 40
VSWR max	1.30	1.40	1.50	1.70	1.90
Insertion loss max	0.30 dB	0.40 dB	0.50 dB	0.70 dB	0.80 dB
Isolation min	70 dB	60 dB	60 dB	55 dB	50 dB
Average power (*)	80 W	60 W	50 W	20 W	10 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING
Nominal current ** : 320 mA

Actuator voltage (Vcc) : 12V (10.2 to 13V) / POSITIVE COMMON

Terminals : 9 pins D-SUB male connector

Indicator rating : 1 W / 30 V / 100 mA
Self cut-off time : 40 ms < CT < 120 ms

MECHANICAL CHARACTERISTICS

Connectors : SMA 2.9 female per MIL-C 39012

Life : 2.5 million cycles

Switching Time*** : < 15 ms

Construction : Splashproof

Weight : < 100 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)







RF input

DPDT Ramses SMA2.9 40GHz Latching Self-cut-off Indicators 12Vdc
Positive common Diodes D-sub connector

PAGE **2/2** ISSUE 06-02-18 SERIE: DPDT PART NUMBER: **R577862017 DRAWING** 0.909 23.10 0.638 □ 16.20 4 x M3 depth 3.50 LABEL 0.909 D-SUB 9 PINS TOP VIEW **RADIALL®** R577862017 0 - 40 GHz Un: 12V Lot : _ _ _ _ [2.205 max.] 56 max. [2.008 max.] 51 max. [0.264 max.] 6.70 max. 4-40 UNC 1.276 □ 32.40 General tolerances: ±0,5 mm [0,02 in] SCHEMATIC DIAGRAM Indicator terminals RF Continuity Voltage Ind. **O** 1 C.1 +C **O** C +C -2 $1 \leftrightarrow 2 \ / \ 3 \leftrightarrow 4$ Actuator **▶**• +C **CUT** 0FF **o** -2

Power input

terminals