Technical Data Sheet



DPDT Ramses SMA 3GHz Latching Indicators 12Vdc Positive common

Pins Terminals with bracket

PAGE 1/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577342010

RF CHARACTERISTICS

Frequency range : 0 - 3 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3
VSWR max	1.20
Insertion loss max	0.20 dB
Isolation min	80 dB
Average power (*)	240 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING
Nominal current ** : 320 mA

Actuator voltage (Vcc) : 12V (10.2 to 13V) / POSITIVE COMMON
Terminals : solder pins (250°C max. / 30 sec.)

Indicator rating : 1 W / 30 V / 100 mA

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 2.5 million cycles

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)









DPDT Ramses SMA 3GHz Latching Indicators 12Vdc Positive common

Pins Terminals with bracket

PAGE 2/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577342010


[0.909] 23.10 [0.638] [0.638] [0.638] [0.638] [0.638] [0.638] [0.638] [0.638] [0.638]





General tolerances: ±0,5 mm [0,02 in]

SCHEMATIC DIAGRAM



LABEL -↑ -2 +8 -↑ -2 -8 RADIALL® R577342010 0 - 3 GHz Un : 12V Lot : ____

Voltage	RF Continuity	Ind.
+C -1	$1 \leftrightarrow 3 / 2 \leftrightarrow 4$	C.1
+C -2	$1 \leftrightarrow 2 \ / \ 3 \leftrightarrow 4$	C.2

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.