### Old Company Name in Catalogs and Other Documents

On April 1<sup>st</sup>, 2010, NEC Electronics Corporation merged with Renesas Technology Corporation, and Renesas Electronics Corporation took over all the business of both companies. Therefore, although the old company name remains in this document, it is a valid Renesas Electronics document. We appreciate your understanding.

Renesas Electronics website: http://www.renesas.com

April 1<sup>st</sup>, 2010 Renesas Electronics Corporation

Issued by: Renesas Electronics Corporation (http://www.renesas.com)

Send any inquiries to http://www.renesas.com/inquiry.



### Notice

- 1. All information included in this document is current as of the date this document is issued. Such information, however, is subject to change without any prior notice. Before purchasing or using any Renesas Electronics products listed herein, please confirm the latest product information with a Renesas Electronics sales office. Also, please pay regular and careful attention to additional and different information to be disclosed by Renesas Electronics such as that disclosed through our website.
- Renesas Electronics does not assume any liability for infringement of patents, copyrights, or other intellectual property rights
  of third parties by or arising from the use of Renesas Electronics products or technical information described in this document.
  No license, express, implied or otherwise, is granted hereby under any patents, copyrights or other intellectual property rights
  of Renesas Electronics or others.
- 3. You should not alter, modify, copy, or otherwise misappropriate any Renesas Electronics product, whether in whole or in part.
- 4. Descriptions of circuits, software and other related information in this document are provided only to illustrate the operation of semiconductor products and application examples. You are fully responsible for the incorporation of these circuits, software, and information in the design of your equipment. Renesas Electronics assumes no responsibility for any losses incurred by you or third parties arising from the use of these circuits, software, or information.
- 5. When exporting the products or technology described in this document, you should comply with the applicable export control laws and regulations and follow the procedures required by such laws and regulations. You should not use Renesas Electronics products or the technology described in this document for any purpose relating to military applications or use by the military, including but not limited to the development of weapons of mass destruction. Renesas Electronics products and technology may not be used for or incorporated into any products or systems whose manufacture, use, or sale is prohibited under any applicable domestic or foreign laws or regulations.
- 6. Renesas Electronics has used reasonable care in preparing the information included in this document, but Renesas Electronics does not warrant that such information is error free. Renesas Electronics assumes no liability whatsoever for any damages incurred by you resulting from errors in or omissions from the information included herein.
- 7. Renesas Electronics products are classified according to the following three quality grades: "Standard", "High Quality", and "Specific". The recommended applications for each Renesas Electronics product depends on the product's quality grade, as indicated below. You must check the quality grade of each Renesas Electronics product before using it in a particular application. You may not use any Renesas Electronics product for any application categorized as "Specific" without the prior written consent of Renesas Electronics. Further, you may not use any Renesas Electronics product for any application for which it is not intended without the prior written consent of Renesas Electronics. Renesas Electronics shall not be in any way liable for any damages or losses incurred by you or third parties arising from the use of any Renesas Electronics product for an application categorized as "Specific" or for which the product is not intended where you have failed to obtain the prior written consent of Renesas Electronics. The quality grade of each Renesas Electronics product is "Standard" unless otherwise expressly specified in a Renesas Electronics data sheets or data books, etc.
  - "Standard": Computers; office equipment; communications equipment; test and measurement equipment; audio and visual equipment; home electronic appliances; machine tools; personal electronic equipment; and industrial robots.
  - "High Quality": Transportation equipment (automobiles, trains, ships, etc.); traffic control systems; anti-disaster systems; anti-crime systems; safety equipment; and medical equipment not specifically designed for life support.
  - "Specific": Aircraft; aerospace equipment; submersible repeaters; nuclear reactor control systems; medical equipment or systems for life support (e.g. artificial life support devices or systems), surgical implantations, or healthcare intervention (e.g. excision, etc.), and any other applications or purposes that pose a direct threat to human life.
- 8. You should use the Renesas Electronics products described in this document within the range specified by Renesas Electronics, especially with respect to the maximum rating, operating supply voltage range, movement power voltage range, heat radiation characteristics, installation and other product characteristics. Renesas Electronics shall have no liability for malfunctions or damages arising out of the use of Renesas Electronics products beyond such specified ranges.
- 9. Although Renesas Electronics endeavors to improve the quality and reliability of its products, semiconductor products have specific characteristics such as the occurrence of failure at a certain rate and malfunctions under certain use conditions. Further, Renesas Electronics products are not subject to radiation resistance design. Please be sure to implement safety measures to guard them against the possibility of physical injury, and injury or damage caused by fire in the event of the failure of a Renesas Electronics product, such as safety design for hardware and software including but not limited to redundancy, fire control and malfunction prevention, appropriate treatment for aging degradation or any other appropriate measures. Because the evaluation of microcomputer software alone is very difficult, please evaluate the safety of the final products or system manufactured by you.
- 10. Please contact a Renesas Electronics sales office for details as to environmental matters such as the environmental compatibility of each Renesas Electronics product. Please use Renesas Electronics products in compliance with all applicable laws and regulations that regulate the inclusion or use of controlled substances, including without limitation, the EU RoHS Directive. Renesas Electronics assumes no liability for damages or losses occurring as a result of your noncompliance with applicable laws and regulations.
- 11. This document may not be reproduced or duplicated, in any form, in whole or in part, without prior written consent of Renesas Electronics
- 12. Please contact a Renesas Electronics sales office if you have any questions regarding the information contained in this document or Renesas Electronics products, or if you have any other inquiries.
- (Note 1) "Renesas Electronics" as used in this document means Renesas Electronics Corporation and also includes its majority-owned subsidiaries.
- (Note 2) "Renesas Electronics product(s)" means any product developed or manufactured by or for Renesas Electronics.



# NEM090603M-28

### N-CHANNEL SILICON POWER LDMOS FET FOR 75 W UHF-BAND SINGLE-END POWER AMPLIFIER

### **DESCRIPTION**

The NEM090603M-28 is an N-channel enhancement-mode lateral diffused MOS FET designed for driver or final stage in 0.8 to 1.0 GHz PA, such as, analog/digital TV-transmitter and GSM/EDGE/D-AMPS/PDC cellular base station amplifiers. Dies are manufactured using our NEWMOS technology (our WSi gate lateral MOS FET), and its nitride surface passivation and triple layer aluminum silicon metallization offer a high degree of reliability.

### **FEATURES**

High 1 dB compression output power : Po (1 dB) = 75 W TYP. (VDS = 28 V, IDset = 550 mA, f = 960 MHz)
 High linear gain : GL = 17.5 dB TYP. (VDS = 28 V, IDset = 550 mA, f = 960 MHz)
 High drain efficiency : pd = 54% TYP. (VDS = 28 V, IDset = 550 mA, f = 960 MHz)

Low intermodulation distortion
 IM<sub>3</sub> = -31 dBc TYP. (Vps = 28 V, Ipset = 550 mA, f = 960/960.1 MHz,

Pout = 45 dBm (2 tones))

- · Excellent thermal stability
- · Low cost hollow plastic packages
- Integrated ESD protection
- Excellent stability against HCI (Hot Carrier Injection)

### **APPLICATIONS**

- Digital cellular base station PA: GSM/EDGE/D-AMPS/PDC/N-CDMA etc.
- UHF-band TV-transmitter PA

### ORDERING INFORMATION

Part Number	Order Number	Package	Supplying Form
NEM090603M-28	NEM090603M-28-A	3M (T-91M) (Pb-Free)	ESD protective tray

Remark To order evaluation samples, contact your nearby sales office.

The unit sample quantity is 1 pcs.

Caution Observe precautions when handling because these devices are sensitive to electrostatic discharge.

The information in this document is subject to change without notice. Before using this document, please confirm that this is the latest version. Not all products and/or types are available in every country. Please check with an NEC Electronics sales representative for availability and additional information.



### ABSOLUTE MAXIMUM RATINGS (TA = +25°C, unless otherwise specified)

Parameter	Symbol	Ratings	Unit
Drain to Source Voltage	Vos	65	V
Gate to Source Voltage	V <sub>G</sub> s	±7	V
Drain Current	ΙD	6	Α
Total Device Dissipation	PD Note 1	146	W
Input Power	Pin Note 2	3.0	W
Channel Temperature	Tch	200	°C
Storage Temperature	Tstg	-65 to +150	°C

Notes 1.  $Tc = 25^{\circ}C$ 

**2.**  $f = 960 \text{ MHz}, V_{DS} = 28 \text{ V}$ 

### RECOMMENDED OPERATING RANGE

Parameter	Symbol	MIN.	TYP.	MAX.	Unit
Drain to Source Voltage	V <sub>DS</sub>	-	28	30	٧
Gate to Source Voltage	V <sub>GS</sub>	2.6	3.0	3.6	V
Average Input Power <sup>Note</sup>	Pin (ave.)	-	28	32	dBm

**Note** f = 960 MHz


### ELECTRICAL CHARACTERISTICS (TA = +25°C)


Parameter	Symbol	Test Conditions	MIN.	TYP.	MAX.	Unit
Gate to Source Leak Current	lgss	V <sub>GSS</sub> = 5 V	-	-	1	μΑ
Saturated Drain Current	IDSS	V <sub>DSS</sub> = 65 V	-	ı	1	mA
Gate Threshold Voltage	Vth	V <sub>DS</sub> = 10 V, I <sub>D</sub> = 1 mA	1.7	2.2	2.8	٧
Transconductance	<b>g</b> m	V <sub>DS</sub> = 28 V, I <sub>Dset</sub> = 550 mA	-	2.7	ı	S
Drain to Source Breakdown Voltage	BV <sub>DSS</sub>	loss = 10 $\mu$ A	65	75	ı	٧
Thermal Resistance	Rth (ch-c)	Channel to Case	_	1.0	1.2	°C/W
Gain 1 dB Compression Output Power	Po (1 dB)	f = 960 MHz, V <sub>DS</sub> = 28 V,	-	48.8	ı	dBm
Linear Gain	GL Note 1	I <sub>Dset</sub> = 550 mA	16	17.5	ı	dB
Output Power	Pout Note 2		47.5	48.3	ı	dBm
Drain Efficiency	$\eta_{ extsf{d}}$		48	54	ı	%
Power Added Efficiency	$\eta$ add		=	53	ı	%
3rd Order Intermodulation Distortion	IM <sub>3</sub>	f = 960/960.1 MHz, V <sub>DS</sub> = 28 V, I <sub>Dset</sub> = 550 mA, 2 tones P <sub>out</sub> = 45 dBm	_	-31	Ι	dBc

Notes 1. Pin = 21 dBm

**2.** Pin = 32 dBm

### TYPICAL CHARACTERISTICS (TA = +25°C, VDS = 28 V, IDset = 550 mA, unless otherwise specified)






**Remark** The graphs indicate nominal characteristics.




## TYPICAL CHARACTERISTICS (TA = +25°C, VDS = 28 V, IDset = 550 mA, EDGE Modulation Spectrum Performance, unless otherwise specified)

SPECTRUM REGROWTH, EVM rms, DRAIN EFFICIENCY vs. OUTPUT POWER




Remark The graph indicates nominal characteristics.

### <R> TYPICAL CHARACTERISTICS (TA = +25°C, unless otherwise specified)



**Remark** The graphs indicate nominal characteristics.



### <R> S-PARAMETERS

S-parameters/Noise parameters are provided on our web site in a form (S2P) that enables direct import to a microwave circuit simulator without keyboard input.

Click here to download S-parameters.


[RF and Microwave] → [Device Parameters]

URL http://www.ncsd.necel.com/microwave/index.html




### <R> PACKAGE DIMENSIONS

3M (T-91M) (UNIT: mm)



### **PIN CONNECTIONS**

- 1. Source
- 2. Drain
- 3. Gate



Remark (): Reference value

6



<R>

### RECOMMENDED MOUNTING CONDITIONS FOR CORRECT USE

- (1) Fix to a heatsink or mount surface completely with screws at the two holes of the flange.
- (2) The recommended torque strength of the screws is 53 N·cm typical using M3 type screws.
- (3) The recommended flatness of the mount surface is less than  $\pm 10~\mu m$  (roughness of surface is  $\nabla \nabla \nabla$ ).

### RECOMMENDED SOLDERING CONDITIONS

This product should be soldered and mounted under the following recommended conditions. For soldering methods and conditions other than those recommended below, contact your nearby sales office.

Soldering Method	Soldering Conditions	Condition Symbol	
Partial Heating	Peak temperature (terminal temperature) Soldering time (per terminal of device) Maximum chlorine content of rosin flux (% mass)	: 350°C or below : 3 seconds or less : 0.2%(Wt.) or below	HS350-P3

Caution Do not use different soldering methods together (except for partial heating).



- The information in this document is current as of October, 2006. The information is subject to change without notice. For actual design-in, refer to the latest publications of NEC Electronics data sheets or data books, etc., for the most up-to-date specifications of NEC Electronics products. Not all products and/or types are available in every country. Please check with an NEC Electronics sales representative for availability and additional information.
- No part of this document may be copied or reproduced in any form or by any means without the prior
  written consent of NEC Electronics. NEC Electronics assumes no responsibility for any errors that may
  appear in this document.
- NEC Electronics does not assume any liability for infringement of patents, copyrights or other intellectual property rights of third parties by or arising from the use of NEC Electronics products listed in this document or any other liability arising from the use of such products. No license, express, implied or otherwise, is granted under any patents, copyrights or other intellectual property rights of NEC Electronics or others.
- Descriptions of circuits, software and other related information in this document are provided for illustrative purposes in semiconductor product operation and application examples. The incorporation of these circuits, software and information in the design of a customer's equipment shall be done under the full responsibility of the customer. NEC Electronics assumes no responsibility for any losses incurred by customers or third parties arising from the use of these circuits, software and information.
- While NEC Electronics endeavors to enhance the quality, reliability and safety of NEC Electronics products, customers agree and acknowledge that the possibility of defects thereof cannot be eliminated entirely. To minimize risks of damage to property or injury (including death) to persons arising from defects in NEC Electronics products, customers must incorporate sufficient safety measures in their design, such as redundancy, fire-containment and anti-failure features.
- NEC Electronics products are classified into the following three quality grades: "Standard", "Special" and
  "Specific".

The "Specific" quality grade applies only to NEC Electronics products developed based on a customer-designated "quality assurance program" for a specific application. The recommended applications of an NEC Electronics product depend on its quality grade, as indicated below. Customers must check the quality grade of each NEC Electronics product before using it in a particular application.

- "Standard": Computers, office equipment, communications equipment, test and measurement equipment, audio and visual equipment, home electronic appliances, machine tools, personal electronic equipment and industrial robots.
- "Special": Transportation equipment (automobiles, trains, ships, etc.), traffic control systems, anti-disaster systems, anti-crime systems, safety equipment and medical equipment (not specifically designed for life support).
- "Specific": Aircraft, aerospace equipment, submersible repeaters, nuclear reactor control systems, life support systems and medical equipment for life support, etc.

The quality grade of NEC Electronics products is "Standard" unless otherwise expressly specified in NEC Electronics data sheets or data books, etc. If customers wish to use NEC Electronics products in applications not intended by NEC Electronics, they must contact an NEC Electronics sales representative in advance to determine NEC Electronics' willingness to support a given application.

### (Note)

- (1) "NEC Electronics" as used in this statement means NEC Electronics Corporation and also includes its majority-owned subsidiaries.
- (2) "NEC Electronics products" means any product developed or manufactured by or for NEC Electronics (as defined above).

M8E 02.11-1

**NEC** NEM090603M-28



### ▶For further information, please contact

### **NEC Compound Semiconductor Devices Hong Kong Limited**

E-mail: contact@ncsd-hk.necel.com

Hong Kong Head Office TEL: +852-3107-7303 FAX: +852-3107-7309
Taipei Branch Office TEL: +886-2-8712-0478 FAX: +886-2-2545-3859
Korea Branch Office TEL: +82-2-558-2120 FAX: +82-2-558-5209

### NEC Electronics (Europe) GmbH http://www.eu.necel.com/

TEL: +49-211-6503-0 FAX: +49-211-6503-1327

California Eastern Laboratories, Inc. http://www.cel.com/

TEL: +1-408-988-3500 FAX: +1-408-988-0279

Compound Semiconductor Devices Division NEC Electronics Corporation URL: http://www.ncsd.necel.com/