Technical Data Sheet



SP4T Terminated Ramses N 3GHz Normally open Indicators 12Vdc

D-sub connector

PAGE 1/2 ISSUE 22-03-22 SERIE : SPnT PART NUMBER : R574012405

RF CHARACTERISTICS

Number of ways : 4

Frequency range : 0 - 3 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3
VSWR max	1.20
Insertion loss max	0.20 dB
Isolation min	80 dB
Average power (*)	400 W

TERMINATION IMPEDANCE : 50 Ohms

TERM. AVG. POWER AT 25° C : 1 W per termination / 3 W total power

ELECTRICAL CHARACTERISTICS

Actuator : NORMALLY OPEN

Nominal current ** : 250 mA

Actuator voltage (Vcc) : 12V (10.2 to 13V) / NEGATIVE COMMON

Terminals : 25 pins D-SUB male connector

Indicator rating : 1 W / 30 V / 100 mA

MECHANICAL CHARACTERISTICS

Connectors : N female per MIL-C 39012
Life : 2 million cycles per position

Switching Time*** : < 15 msConstruction : Splashproof
Weight : < 460 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)



Technical Data Sheet




SP4T Terminated Ramses N 3GHz Normally open Indicators 12Vdc


D-sub connector

PAGE 2/2 ISSUE 22-03-22 SERIE : SPnT PART NUMBER : R574012405

DRAWING




Voltage	RF Continuity	Ind.
-C +1	$IN \leftrightarrow 1$	D.E
-C +2	$IN \leftrightarrow 2$	D.F
-C +3	$IN \leftrightarrow 3$	D.G
-C +4	$IN \leftrightarrow 4$	D.H




General tolerances: ±0,5 mm [0,02 in]

LABEL



SCHEMATIC DIAGRAM



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.