Technical Data Sheet



DP3T Ramses SMA 3GHz Normally open 12Vdc TTL Diodes Pins terminals

PAGE 1/2 ISSUE 09-03-21 SERIE : DP3T PART NUMBER : R585372100

RF CHARACTERISTICS

Frequency range : 0 - 3 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3
VSWR max	1.20
Insertion loss max	0.20 dB
Isolation min	80 dB
Average power (*)	240 W

ELECTRICAL CHARACTERISTICS

Actuator : NORMALLY OPEN

Nominal current ** : 250 mA

Actuator voltage (Vcc) : 12V (10.2 to 13V)

Terminals : solder pins (250°C max. / 30 sec.)

TTL inputs (E) - High level : 2.2 to 5.5 V / $800\mu A$ at 5.5 V

- Low level : 0 to 0.8 V / 20µA at 0.8 V

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 2 million cycles

Switching Time*** : < 10 ms

Construction : Splashproof

Weight : < 100 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)



Technical Data Sheet



DP3T Ramses SMA 3GHz Normally open 12Vdc TTL Diodes Pins terminals

