SIEMENS

Data sheet



Coordinate switch, 22 mm, round, plastic with metal front ring, black, 2 switch positions, horizontal momentary contact type, without mechanical interlocking, in O position, with holder, 1 NO, 1 NO, screw terminal, Z=20-unit packaging

product designationCoordinate switchesdesign of the productComplete unitproduct type designation3SU1product linePlastic with metal front ring, matt, 22 mmmanufacturer's article number		
product type designation product line Plastic with metal front ring, matt, 22 mm manufacturer's article number of supplied contact module at position 2 of supplied contact module at position 4 of the supplied holder of the supplied actuator Enclosure shape of the enclosure front 3SU1 201400-1AA10-1BA0 3SU1400-1AA10-1BA0 3SU1400-1AA10-1BA0 3SU1550-0BA10-0AA0 3SU1030-7AD10-0AA0 Enclosure shape of the enclosure front		
product line Plastic with metal front ring, matt, 22 mm manufacturer's article number of supplied contact module at position 2 of supplied contact module at position 4 of the supplied holder of the supplied actuator Enclosure shape of the enclosure front Plastic with metal front ring, matt, 22 mm 3SU1400-1AA10-1BA0 3SU1400-1AA10-1BA0 3SU1400-1AA10-1BA0 3SU1550-0BA10-0AA0 3SU1030-7AD10-0AA0 Enclosure		
manufacturer's article number of supplied contact module at position 2 of supplied contact module at position 4 of the supplied holder of the supplied actuator Shape of the enclosure front assultano-1AA10-1BA0 assult		
of supplied contact module at position 2 of supplied contact module at position 4 of the supplied holder of the supplied actuator of the supplied actuator shape of the enclosure front 3SU1400-1AA10-1BA0 3SU1550-0BA10-0AA0 3SU1030-7AD10-0AA0 round		
of supplied contact module at position 4 of the supplied holder of the supplied actuator of the supplied actuator SU1030-7AD10-0AA0 Enclosure shape of the enclosure front round		
 of the supplied holder of the supplied actuator SU1030-7AD10-0AA0 Enclosure shape of the enclosure front 		
of the supplied actuator 3SU1030-7AD10-0AA0 Enclosure shape of the enclosure front round		
Enclosure shape of the enclosure front round		
shape of the enclosure front round		
·		
Actuator		
design of the actuating element without mechanical interlock		
principle of operation of the actuating element momentary contact type		
direction of actuation vertical		
product extension optional light source No		
color of the actuating element black		
material of the actuating element plastic		
shape of the actuating element Extended handle		
outer diameter of the actuating element 30.5 mm		
number of contact modules 2		
number of switching positions 2		
Maximum deflection angle [°] 30°		
Front ring		
product component front ring Yes		
design of the front ring high		
material of the front ring Metal, matt		
color of the front ring sand gray		
Holder		
material of the holder Plastic		
General technical data		
product function positive opening No		
insulation voltage rated value 500 V		
degree of pollution 3		
type of voltage of the operating voltage AC/DC		
surge voltage resistance rated value 6 kV		
protection class IP IP65, IP67		
• of the terminal IP20		

shock resistance	
• according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
vibration resistance	
according to IEC 60068-2-6	10 500 Hz: 5g
operating frequency maximum	2 400 1/h
mechanical service life (switching cycles)	
as operating period per direction of actuation typical	500 000
electrical endurance (switching cycles) typical	10 000 000
electrical endurance (switching cycles) with contactors 3RT1015 to 3RT1026 typical	10 000 000
thermal current	10 A
reference code according to IEC 81346-2	S
continuous current of the C characteristic MCB	10 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A
continuous current of the DIAZED fuse link gG	10 A
Substance Prohibitance (Date)	10/01/2014
operating voltage	
• at AC	
— at 50 Hz rated value	5 500 V
— at 60 Hz rated value	5 500 V
at DC rated value	5 500 V
Power Electronics	
contact reliability	One maloperation per 100 million (17 V, 5 mA), one maloperation per 10 million (5 V, 1 mA)
Auxiliary circuit	
design of the contact of auxiliary contacts	Silver alloy
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	2
Connections/ Terminals	
type of electrical connection of modules and accessories	Screw-type terminal
type of connectable conductor cross-sections	Screw-type terminal
solid with core end processing	2v (0.5 0.75 mm²)
	2x (0.5 0.75 mm²)
solid without core end processing finely stranded with core and processing	2x (1.0 1.5 mm²)
 finely stranded with core end processing finely stranded without core end processing 	2x (0.5 1.5 mm²)
, ,	2x (1,0 1,5 mm²)
at AWG cables tightening targue of the garage in the broadet.	2x (18 14)
tightening torque of the screws in the bracket	1 1.2 N·m
tightening torque for auxiliary contacts with screw-type terminals	0.8 1 N·m
Safety related data	
B10 value with high demand rate according to SN 31920	250 000
proportion of dangerous failures	
 with low demand rate according to SN 31920 	20 %
with high demand rate according to SN 31920	20 %
failure rate [FIT] with low demand rate according to SN 31920	100 FIT
Ambient conditions	
ambient temperature	
during operation	-25 +70 °C
during storage	-40 +80 °C
environmental category during operation according to IEC 60721	3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 95%, no condensation in operation permitted for all devices behind front panel)
Installation/ mounting/ dimensions	
fastening method	front plate mounting
of modules and accessories	Front plate mounting
height	40 mm
width	40 mm
shape of the installation opening	round
mounting diameter	22.3 mm
positive tolerance of installation diameter	0.4 mm
positive tolerance of installation dialifeter	V.T HIIII

mounting height	71.3 mm
installation width	30.5 mm
installation depth	53.7 mm

Certificates/ approvals

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1130-7AD10-1NA0-Z X90


Cax online generator


http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1130-7AD10-1NA0-Z X90


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SU1130-7AD10-1NA0-Z X90

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1130-7AD10-1NA0-Z X90&lang=en







last modified:

1/27/2022