## **Technical Data Sheet**



DPDT Ramses SMA 3GHz Latching Indicators 28Vdc Positive common

Pins Terminals with bracket

PAGE 1/2 ISSUE 10-07-19 SERIE : DPDT PART NUMBER : R577343010

## RF CHARACTERISTICS

Frequency range : 0 - 3 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3
VSWR max	1.20
Insertion loss max	0.20 dB
Isolation min	80 dB
Average power (*)	240 W

## **ELECTRICAL CHARACTERISTICS**

Actuator : LATCHING
Nominal current \*\* : 125 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / POSITIVE COMMON
Terminals : solder pins (250°C max. / 30 sec.)

Indicator rating : 1 W / 30 V / 100 mA

## MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 2.5 million cycles

Switching Time\*\*\* : < 15 ms

Construction : Splashproof

Weight : < 100 g

## ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(\* Average power at 25°C per RF Path)

(\*\* At 25° C ±10%)

(\*\*\* Nominal voltage; 25° C)









DPDT Ramses SMA 3GHz Latching Indicators 28Vdc Positive common

Pins Terminals with bracket

PAGE **2/2** ISSUE 10-07-19 SERIE: DPDT PART NUMBER: **R577343010** 


# **DRAWING** [0.909] 23.10 0.638 □້16.20 4 x M3 depth 3.50 [0.909] 23.10





General tolerances: ±0,5 mm [0,02 in]

## SCHEMATIC DIAGRAM



## **LABEL** 1 2 +C 1 2 C **RADIALL®** R577343010 0 - 3 GHz Un: 28V Lot : \_ \_ \_ \_

Voltage	RF Continuity	Ind.
+C -1	$1 \leftrightarrow 3 / 2 \leftrightarrow 4$	C.1
+C -2	$1 \leftrightarrow 2 \ / \ 3 \leftrightarrow 4$	C.2

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.