SIEMENS

Data sheet



Coordinate switch, 22 mm, round, plastic with metal front ring, black, 2 switch positions, horizontal, momentary contact type, with mechanical interlocking in O position, with holder, 1 NO, 1 NO, screw terminal, with laser labeling, upper case

product brand name	SIRIUS ACT	
product designation	Coordinate switches	
design of the product	Complete unit	
product type designation	3SU1	
product line	Plastic with metal front ring, matt, 22 mm	
manufacturer's article number	<u> </u>	
 of supplied contact module at position 1 	3SU1400-1AA10-1BA0	
 of supplied contact module at position 3 	3SU1400-1AA10-1BA0	
of the supplied holder	3SU1550-0BA10-0AA0	
of the supplied actuator	3SU1030-7BC10-0AA0	
Enclosure		
shape of the enclosure front	round	
Actuator		
design of the actuating element	with mechanical interlocking	
principle of operation of the actuating element	momentary contact type	
direction of actuation	horizontal	
product extension optional light source	No	
color of the actuating element	black	
material of the actuating element	plastic	
shape of the actuating element	Extended handle	
outer diameter of the actuating element	30.5 mm	
marking of the actuating element	Any inscription, text in upper case	
number of contact modules	2	
type of unlocking device	push-to-unlatch mechanism	
number of switching positions	2	
Maximum deflection angle [°]	30°	
Front ring		
product component front ring	Yes	
design of the front ring	high	
material of the front ring	Metal, matt	
color of the front ring	sand gray	
Holder		
material of the holder	Plastic	
General technical data		
product function positive opening	No	
insulation voltage rated value	500 V	
degree of pollution	3	
type of voltage of the operating voltage	AC/DC	
surge voltage resistance rated value	6 kV	

protection class IP	IP65, IP67
of the terminal	IP20
shock resistance	
according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
vibration resistance	
according to IEC 60068-2-6	10 500 Hz: 5g
operating frequency maximum	2 400 1/h
mechanical service life (switching cycles)	
as operating period per direction of actuation typical	500 000
electrical endurance (switching cycles) typical	10 000 000
electrical endurance (switching cycles) with	10 000 000
contactors 3RT1015 to 3RT1026 typical	
thermal current	10 A
reference code according to IEC 81346-2	S
continuous current of the C characteristic MCB	10 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A
continuous current of the DIAZED fuse link gG	10 A
Substance Prohibitance (Date)	10/01/2014
operating voltage	
• at AC	
— at 50 Hz rated value	5 500 V
— at 60 Hz rated value	5 500 V
• at DC rated value	5 500 V
Power Electronics	
contact reliability	One maloperation per 100 million (17 V, 5 mA), one maloperation per 10
·	million (5 V, 1 mA)
Auxiliary circuit	
design of the contact of auxiliary contacts	Silver alloy
number of NC contacts for auxiliary contacts	0
number of NO contacts for auxiliary contacts	2
Connections/ Terminals	
type of electrical connection of modules and accessories	Screw-type terminal
type of connectable conductor cross-sections	, , , , , , , , , , , , , , , , , , ,
solid with core end processing	2x (0.5 0.75 mm²)
solid without core end processing	2x (1.0 1.5 mm²)
finely stranded with core end processing	2x (0.5 1.5 mm²)
finely stranded with core end processing finely stranded without core end processing	2x (1.0 1.5 mm²)
at AWG cables	2x (1,0 1,5 mm) 2x (18 14)
tightening torque of the screws in the bracket	1 1.2 N·m
tightening torque for auxiliary contacts with screw-type	0.8 1 N·m
terminals	V.O 1 IV III
Safety related data	
B10 value with high demand rate according to SN 31920	250 000
proportion of dangerous failures	
with low demand rate according to SN 31920	20 %
with low demand rate according to SN 31920 with high demand rate according to SN 31920	20 %
failure rate [FIT] with low demand rate according to SN	100 FIT
31920	100111
Ambient conditions	
ambient temperature	
during operation	-25 +70 °C
during operation during storage	-40 +80 °C
environmental category during operation according to IEC	3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 95%, no
60721	condensation in operation permitted for all devices behind front panel)
Installation/ mounting/ dimensions	, and a second s
fastening method	front plate mounting
of modules and accessories	Front plate mounting Front plate mounting
height	40 mm
width	40 mm
shape of the installation opening	40 mm round

22.3 mm	
0.4 mm	
75.6 mm	
30.5 mm	
53.7 mm	
Certificates/ approvals	

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1130-7BC10-1NA0-Z Y11

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1130-7BC10-1NA0-Z Y11

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3SU1130-7BC10-1NA0-Z Y11

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1130-7BC10-1NA0-Z Y11&lang=en

last modified: 1/27/2022 🖸