Technical Data Sheet



DPDT Ramses BNC 3GHz Failsafe 28Vdc D-sub connector with bracket

PAGE 1/2 | ISSUE 22-03-22 | SERIE : DPDT | PART NUMBER : R577213005

RF CHARACTERISTICS

Frequency range : 0 - 3 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 1	1 - 2	2 - 3
VSWR max	1.15	1.20	1.25
Insertion loss max	0.15 dB	0.20 dB	0.25 dB
Isolation min	85 dB	80 dB	75 dB
Average power (*)	400 W	300 W	240 W

ELECTRICAL CHARACTERISTICS

Actuator : FAILSAFE
Nominal current ** : 140 mA

Actuator voltage (Vcc) : 28V (24 to 30V)

Terminals : 9 pins D-SUB male connector

MECHANICAL CHARACTERISTICS

Connectors : BNC female per MIL-C 39012

Life : 2.5 million cycles

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.


Technical Data Sheet



DPDT Ramses BNC 3GHz Failsafe 28Vdc D-sub connector with bracket

PAGE 2/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577213005

DRAWING



LABEL


D - SUB 9 PINS TOP VIEW

RADIALL® R577213005 0 - 3 GHz Un : 28V Lot : _ _ _ _

General tolerances: ±0,5 mm [0,02 in]

SCHEMATIC DIAGRAM

Position: De energized



Voltage	RF Continuity
energized	$1 \leftrightarrow 3 / 2 \leftrightarrow 4$
De-energized	$1 \leftrightarrow 2 / 3 \leftrightarrow 4$