



SPDT Terminated Ramses SMA 18GHz Latching Self-cut-off Indicators 28Vdc Diodes Internal loads Pins terminals

PAGE 1/2 ISSUE 09-03-21 SERIE : SPDT ZC PART NUMBER : R585463200

RF CHARACTERISTICS

Frequency range : 0 - 18 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18
VSWR max	1.20	1.30	1.40	1.50
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB
Isolation min	80 dB	70 dB	60 dB	60 dB
Average power (*)	240 W	150 W	120 W	100 W

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING
Nominal current ** : 160 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / NEGATIVE COMMON Terminals : solder pins (250°C max. / 30 sec.)

 $\begin{array}{ll} \text{Indicator rating} & : \ 1 \ \text{W} \ / \ 30 \ \text{V} \ / \ 100 \ \text{mA} \\ \text{Self cut-off time} & : \ 40 \ \text{ms} < \text{CT} < 120 \ \text{ms} \end{array}$

MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 2 million cycles

Switching Time*** : < 10 ms

Construction : Splashproof

Weight : < 100 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)







 50Ω Termination

SPDT Terminated Ramses SMA 18GHz Latching Self-cut-off Indicators 28Vdc Diodes Internal loads Pins terminals

PAGE **2/2** ISSUE **09-03-21** SERIE: SPDT ZC PART NUMBER: **R585463200 DRAWING** [2.189] 55.6 0.44 0.44 11.18 11.18 [0.138 min.] LABEL 3.5 min. +2 2 -C 0 - 18 GHz Un: 28V **RADIALL®** R585463200 Lot : _ _ _ _ [0.122][0.094]С 1 4 x ¯ Ø 3.1 [0.059 max.] 1.5 max. [0.303 max.] 7.7 max. [0.441] 11.2 [1.321] 33.55 **@@@ %** 00 0 General tolerances: ±0,5 mm [0,02 in] **SCHEMATIC DIAGRAM** Indicator terminals RF input -02 50Ω Termination Actuator RF Continuity Voltage Ind. ¥₩0-С -C C↔1 / 2↔50Ω -C +2 $C\leftrightarrow 2/1\leftrightarrow 50\Omega$ **→**0-C CUT OFF Power input ∞ terminals ₹W0-0