



DPDT Ramses DIN 2.5GHz Latching Self-cut-off 12Vdc Positive common Diodes Pins Terminals

PAGE 1/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577952012

### RF CHARACTERISTICS

Frequency range : 0 - 2.5 GHz Impedance : 75 Ohms

Frequency (GHz)	DC - 1	1 - 2.5
VSWR max	1.20	1.30
Insertion loss max	0.20 dB	0.30 dB
Isolation min	80 dB	70 dB
Average power (*)	400 W	240 W

#### **ELECTRICAL CHARACTERISTICS**

Actuator : LATCHING
Nominal current \*\* : 320 mA

Actuator voltage (Vcc) : 12V (10.2 to 13V) / POSITIVE COMMON Terminals : solder pins (250°C max. / 30 sec.)

Self cut-off time : 40 ms < CT < 120 ms

### MECHANICAL CHARACTERISTICS

Connectors : 1.6/5.6 female per IEC 169-13

Life : 2.5 million cycles

Switching Time\*\*\* : < 15 ms

Construction : Splashproof

Weight : < 100 g

## **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range :  $-25^{\circ}$ C to  $+70^{\circ}$ C Storage temperature range :  $-40^{\circ}$ C to  $+85^{\circ}$ C

(\* Average power at 25°C per RF Path)

(\*\* At 25° C ±10%)

(\*\*\* Nominal voltage; 25° C)








DPDT Ramses DIN 2.5GHz Latching Self-cut-off 12Vdc Positive common Diodes Pins Terminals

PAGE 2/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577952012

#### **DRAWING**





# LABEL


-1 -2 +C


RADIALL®

R577952012
0 - 2.5 GHz

Un : 12V


Un : 12V Lot : \_ \_ \_ \_





General tolerances: ±0,5 mm [0,02 in]

# SCHEMATIC DIAGRAM



Voltage	RF Continuity	
+C -1	$1 \leftrightarrow 3 / 2 \leftrightarrow 4$	
+C -2	$1 \leftrightarrow 2 / 3 \leftrightarrow 4$	