


Description: 868-928MHz

PART NUMBER: W5021

Series: Stick Antenna





All dimensions are in mm / inches

Features:

- ¼ wave dipole antenna
- Length 180mm
- Gain 2.2 dBi
- Connector Right Angle RP SMA
- High Efficiency >70%
- Power rating 1W
- IP65 rated

Applications:

- ISM 868 / 915 MHz radios
- IoT, M2M
- Industry automation
- · Remote controls
- Toys, Consumer electronics

Issue: 1637

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:

Pulse Worldwide Headquarters 12220 World Trade Drive San Diego, CA 92128 USA Tel:1-858-674-8100 Pulse/Larsen Antennas 3611 NE 112th Ave Vancouver, WA 98682 USA Tel: 1-360-944-7551 Europe Headquarters Pulse GmbH & Do, KG Zeppelinstrasse 15 Herrenberg, Germany Tel: 49 7032 7806 0 Pulse (Suzhou) Wireless Products Co, Inc. 99 Huo Ju Road(#29 Bldg,4th Phase Suzhou New District Jiangsu Province, Suzhou 215009 PR China Tel: 86 512 6807 9998



Description: 868-928MHz

Series: Stick Antenna

PART NUMBER: W5021

ELECTRICAL SPECIFICATIONS		
Frequency	868-928	MHz
Nominal Impedance	50	Ω
VSWR	2	Max
Average efficiency	70	%
Peak Gain	2.2	dBi +/- 1 dB
Polarization:	Vertical	
Power withstanding	1	W
Connector type	RP-SMA	



Description: 868-928MHz

Series: Stick Antenna

PART NUMBER: W5021

MECHANICAL SPECIFICATIONS

Plastic radome TPEE

Color Black

Ingress Protection IP65

Weight 22.8 g

Overall Length 180mm/7.09Inches

ENVIRONMENTAL SPECIFICATIONS

Operating temperature

-40/+85° C






Description: 868-928MHz

Series: Stick Antenna

PART NUMBER: W5021

MECHANICAL DRAWING





Description: 868-928MHz


Series: Stick Antenna

PART NUMBER: W5021

CHARTS

VSWR

VSWR vs Frequency measured in free space W5021 measured in PSU







Description: 868-928MHz


Series: Stick Antenna

PART NUMBER: W5021

CHARTS

Efficiency

Efficiency vs Frequency measured in free space W5021 measured in PSU



-W5021





Series: Stick Antenna

TECHNICAL DATA SHEET


Description: 868-928MHz

PART NUMBER: W5021

CHARTS

Peak Gain

Peak Gain vs Frequency measured in free space W5021 measured in PSU








Description: 868-928MHz

Series: Stick Antenna
PART NUMBER: W5021

CHARTS






Description: 868-928MHz

Series: Stick Antenna
PART NUMBER: W5021

CHARTS



Issue: 1637






Description: 868-928MHz

Series: Stick Antenna

PART NUMBER: W5021

CHARTS



Issue: 1637





Description: 868-928MHz

Series: Stick Antenna

PART NUMBER: W5021

PACKAGING

600PCS/Carton box