



DPDT Ramses SMA 26.5GHz Latching Indicators 28Vdc Positive common

Diodes D-sub connector with bracket

PAGE 1/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577F43045

### **RF CHARACTERISTICS**

Frequency range : 0 - 26.5 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3	3 - 8	8 - 12.4	12.4 - 18	18 - 26.5
VSWR max	1.20	1.30	1.40	1.50	1.70
Insertion loss max	0.20 dB	0.30 dB	0.40 dB	0.50 dB	0.70 dB
Isolation min	80 dB	70 dB	65 dB	60 dB	50 dB
Average power (*)	240 W	150 W	120 W	100 W	40 W

### **ELECTRICAL CHARACTERISTICS**

Actuator : LATCHING
Nominal current \*\* : 125 mA

Actuator voltage (Vcc) : 28V (24 to 30V) / POSITIVE COMMON

Terminals : 9 pins D-SUB male connector

Indicator rating : 1 W / 30 V / 100 mA

## MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 2.5 million cycles

Switching Time\*\*\* : <15 ms

Construction : Splashproof

Weight : <100 g

# **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(\* Average power at 25°C per RF Path)

(\*\* At 25° C ±10%)

(\*\*\* Nominal voltage; 25° C)










DPDT Ramses SMA 26.5GHz Latching Indicators 28Vdc Positive common Diodes D-sub connector with bracket

PAGE 2/2 ISSUE 22-03-22 SERIE : DPDT PART NUMBER : R577F43045

#### **DRAWING**









General tolerances: ±0,5 mm [0,02 in]

## SCHEMATIC DIAGRAM





# LABEL



RADIALL® R577F43045 0 - 26.5 GHz Un : 28V Lot : \_ \_ \_