
Radiall 狐		Technical Data Sheet DPDT Ramses DIN 2.5GHz Latching Indicators 28Vdc D-sub connector with bracket	
PAGE <b>1/2</b>	ISSUE 22-03-22	SERIE : <b>DPDT</b>	PART NUMBER : <b>R577943005</b>
RF CHARACTEF	RISTICS		
Frequency		: 0 - 2.5 GH	z
Impedance	9	: 75 Ohms	
Frequency		1 - 2.5	
VSWR ma		1.30 0.30 dB	
Isolation m		70 dB	
Average p		240 W	
ELECTRICAL CH	HARACTERISTICS		G
Nominal current **		: 125 mA	
	oltage (Vcc)		30V) / NEGATIVE COMMON
Terminals Indicator ra	ating	∷ 9 pins D-\$ ∷ 1 W / 30 V	SUB male connector
Connectors Life Switching Time*** Construction Weight		∷ 1.6/5.6 fer ∷ 2.5 million ∷ < 15 ms ∷ Splashpro ∷ < 100 g	
ENVIRONMENT	AL CHARACTERISTICS		
	temperature range	: -25°C to +	
Storage te	mperature range	: -40°C to +	-85°C
	ower at 25°C per RF Path)		
(** At 25° C ± (*** Nominal v	10%) oltage ; 25° C)		OMPLIAT
	5.630,20 0)		

This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.