



SPDT Terminated Ramses SMA 3GHz Latching Indicators 12Vdc Positive common Diodes Internal loads Pins terminals

PAGE 1/2 ISSUE 09-03-21 SERIE : SPDT ZC PART NUMBER : R585342240

## **RF CHARACTERISTICS**

Frequency range : 0 - 3 GHz Impedance : 50 Ohms

Frequency (GHz)	DC - 3
VSWR max	1.20
Insertion loss max	0.20 dB
Isolation min	80 dB
Average power (*)	240 W

## **ELECTRICAL CHARACTERISTICS**

Actuator : LATCHING
Nominal current \*\* : 420 mA

Actuator voltage (Vcc) : 12V (10.2 to 13V) / POSITIVE COMMON
Terminals : solder pins (250°C max. / 30 sec.)
Indicator rating : 1 W / 30 V / 100 mA

## MECHANICAL CHARACTERISTICS

Connectors : SMA female per MIL-C 39012

Life : 2 million cycles

Switching Time\*\*\* : < 10 ms

Construction : Splashproof

Weight : < 100 g

## **ENVIRONMENTAL CHARACTERISTICS**

Operating temperature range : -40°C to +85°C
Storage temperature range : -55°C to +85°C

(\* Average power at 25°C per RF Path)

(\*\* At 25° C ±10%)

(\*\*\* Nominal voltage; 25° C)







SPDT Terminated Ramses SMA 3GHz Latching Indicators 12Vdc Positive common Diodes Internal loads Pins terminals

PAGE **2/2** ISSUE **09-03-21** SERIE: SPDT ZC PART NUMBER: **R585342240 DRAWING** [2.189] 55.6 0.44 0.44 11.18 11.18 [0.138 min.] **LABEL** 3.5 min. •C 0 - 3 GHz Un: 12V **RADIALL®** R585342240 Lot : \_ \_ \_ \_ [0.122][0.094]С 1 4 x ¯ Ø 3.1 [0.059 max.] 1.5 max. [0.303 max.] 7 7 max [0.441] 11.2 [1.321] 33.55 **@@@ %** 00 0 General tolerances: ±0,5 mm [0,02 in] **SCHEMATIC DIAGRAM** Indicator terminals RF input -01 -02  $50\Omega$  Termination -O C Actuator RF Continuity Voltage Ind. ₹W0 С +C C↔1 / 2↔50Ω 0-1 +C -2  $C\leftrightarrow 2/1\leftrightarrow 50\Omega$ **4**0+C -0-5 Power input terminals  $\infty$ \$W0-0  $50\Omega$  Termination