Technical Data Sheet



SP3T Ramses SMA2.9 40GHz Latching 12Vdc Positive common Pins Terminals

PAGE 1/2 ISSUE 09-04-19 SERIE : SPnT PART NUMBER : R573822310

RF CHARACTERISTICS

Number of ways : 3

Frequency range : 0 - 40 GHz Impedance : 50 Ohms

| Frequency (GHz) | DC - 6 | 6 - 12.4 | 12.4 - 18 | 18 - 26.5 | 26.5 - 40 |
|--------------------|---------|----------|-----------|-----------|-----------|
| VSWR max | 1.30 | 1.40 | 1.50 | 1.70 | 2.20 |
| Insertion loss max | 0.20 dB | 0.40 dB | 0.50 dB | 0.70 dB | 1.10 dB |
| Isolation min | 70 dB | 60 dB | 60 dB | 55 dB | 50 dB |
| Average power (*) | 40 W | 30 W | 25 W | 15 W | 5 W |

ELECTRICAL CHARACTERISTICS

Actuator : LATCHING

Nominal current ** : 320 mA / RESET : 960 mA ****

Actuator voltage (Vcc) : 12V (10.2 to 13V) / POSITIVE COMMON Terminals : solder pins (250°C max. / 30 sec.)

MECHANICAL CHARACTERISTICS

Connectors : SMA 2.9 female per MIL-C 39012
Life : 2 million cycles per position

Switching Time*** : <15 ms

Construction : Splashproof

Weight : <180 g

ENVIRONMENTAL CHARACTERISTICS

Operating temperature range : -40°C to +85°C Storage temperature range : -55°C to +85°C

(* Average power at 25°C per RF Path)

(** At 25° C ±10%)

(*** Nominal voltage; 25° C)

(**** Reset : supply voltage time 1sec. max. / duty cycle 10%)




Technical Data Sheet




SP3T Ramses SMA2.9 40GHz Latching 12Vdc Positive common Pins Terminals


PAGE 2/2 ISSUE 09-04-19 SERIE : SPnT PART NUMBER : R573822310

DRAWING




| Voltage | RF Continuity | | |
|-----------|------------------------|--|--|
| +C -RESET | All ports open | | |
| +C -1 | IN ↔ 1 | | |
| +C -2 | IN ↔ 2 | | |
| +C -3 | $IN \leftrightarrow 3$ | | |





General tolerances: ±0,5 mm [0,02 in]

SCHEMATIC DIAGRAM



This document contains proprietary information and such information shall not be disclosed to any third party for any purpose whatsoever or used for manufacturing purposes without prior written agreement from Radiall. The data defined in this document are given as an indication, in the effort to improve our products; we reserve the right to make any changes judged necessary.