

#### APRA1804G3Z

Request Samples



Check Inventory (>)



18 x 18 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

## **Features**

- Complies with Automotive Qualification (AEC-Q200)
- Complies with IATF 16949 Certification
- Multiband GNSS patch with GPS/GLONASS/BeiDou/Galileo
- Low Return loss
- RHCP polarization
- Wide operating temperature ( $-40^{\circ}$ C to  $+105^{\circ}$ C)
- Peak Gain of 4.7 dBi
  - o GPS: 2.5 dBi
  - GLONASS: 4.7 dBi
  - BeiDou: 3.5 dBi

# **Applications**

- **GNSS** applications
- Automotive
- IoT, M2M, V2X
  - o Industrial IoT
    - Infrastructure IoT
    - Consumer IoT
- Navigation
- Logistics
- Geofencing
- Remote monitoring
- Surveying and mapping systems

#### **Product Dimension**







### APRA1804G3Z

Request Samples (>)



Check Inventory (>)



18 x 18 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

# **Electrical Specifications**

Parameter		Unit		
Operating Band	GPS / Galileo	GLONASS	BeiDou	
Operating Frequency	$1575.42 \pm 1.023$	$1602 \pm 5$	$1561.098 \pm 2.046$	MHz
Peak Gain	2.0	4.0	3.0	dBi
Max VSWR				
Impedance		Ω		
Polarization				

#### Note:

Ground Plane size: 70 x 70 mm

Actual Electrical Value will depend on the size of ground plane in use

# **Mechanical Specifications**

Parameter	Specification
Antenna Dimension	18 x 18 x 4 mm
Material	Ceramic
Termination	Silver
Mounting Type	Through-Hole + Adhesive Tape

## **Environmental Specifications**

Parameter	Specification
Operating Temperature	-40°C to +105°C
Storage Temperature	-40 C to +103 C
Frequency Temperature Coefficient (T <sub>f</sub> )	$-40  ^{\circ}\text{C} \text{ to } +105  ^{\circ}\text{C}  (0 \pm 20  \text{ppm/}  ^{\circ}\text{C}  )$
RoHS / RoHS II Compliant	Yes
MSL	1
Environmentally Friendly	Pb free
Relative Humidity	0~95%





### APRA1804G3Z

Request Samples (>)



Check Inventory (>)




18 x 18 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

### **Product Marking**



### **Product Dimension**



Unit: mm





## APRA1804G3Z





Check Inventory (>)




18 x 18 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

# **Layout Dimensions**

Top Side Ground ØЗ Ø0.95 Thru hole


Bottom Side



 $TOL:\pm0.2$ 

Unit: mm

### **Tape Dimensions**



NITTO – NO.5015 | Double-coated thin adhesive tape | Thickness : 0.12 mm

Unit: mm



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

**REVISED: 07-16-21** 

ABRACON IS ISO9001-2015 CERTIFIED



### APRA1804G3Z

Request Samples (>)




Check Inventory (>)




18 x 18 x 4.0 mm RoHS/RoHS II Compliant MSL Level = 1

# VNA Test Measurement – Set up




## Radiation Measurement - Set up

XZ-Plane



YZ-Plane







APRA1804G3Z

Request Samples (>)




Check Inventory (>)



18 x 18 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

### **Test Measurement – Return Loss**







### APRA1804G3Z

Request Samples (>)




Check Inventory (>)



18 x 18 x 4.0 mm RoHS/RoHS II Compliant MSL Level = 1

#### Radiation Measurement — 2D Pattern

# **XZ + YZ Plane : 1575.42 MHz**



Patt	tern	Test Mode	Freq(MHz)	Max Gain(dBi)	Min Gain(dBi)	Avg. Gain(dBi)	Source Polar.
1		XZ	1575.42	2.57 / 358.99	-8.44 / 113.58	-1.97	V+H
1 2		YZ	1575.42	2.56 / 358.99	-10.26 / 126.05	-2.07	V+H





### APRA1804G3Z

Request Samples (>)




Check Inventory (>)



18 x 18 x 4.0 mm RoHS/RoHS II Compliant MSL Level = 1

# **XZ + YZ - Plane : 1561 MHz**



Patt	ern	Test Mode	Freq(MHz)	Max Gain(dBi)	Min Gain(dBi)	Avg. Gain(dBi)	Source Polar.
1		XZ	1561.00	3.32 / 358.99	-8.68 / 110.54	-1.18	V+H
2		YZ	1561.00	3.45 / 358.99	-7.91 / 124.03	-1.11	V+H





### APRA1804G3Z

Request Samples (>)




Check Inventory (>)



18 x 18 x 4.0 mm RoHS/RoHS II Compliant MSL Level = 1

# XZ + YZ - Plane: 1602 MHz



Patte	rn Test Mode	Freq(MHz)	Max Gain(dBi)	Min Gain(dBi)	Avg. Gain(dBi)	Source Polar.
1 2	XZ	1602.00	4.72 / 358.99	-7.34 / 116.62	0.08	V+H
2	YZ	1602.00	4.52 / 0.00	-7.37 / 120.00	-0.08	V+H





### APRA1804G3Z

Request Samples (>)




Check Inventory (>)



18 x 18 x 4.0 mm RoHS/RoHS II Compliant MSL Level = 1

### **Axial Ratio**

# 1575.42 MHz



	2000	Test Mode	Freq(MHz)	Max Gain(dBi)	Min Gain(dBi)	Avg. Gain(dBi)	Source Polar.
1		Axial Ratio	1575.42	2.07 / 358.60	-42.48 / 253.60	-5.27	СР





APRA1804G3Z

Request Samples (>)




Check Inventory (>)



18 x 18 x 4.0 mm RoHS/RoHS II Compliant MSL Level = 1

# 1561 MHz



Patt	ern	Test Mode	Freq(MHz)	Max Gain(dBi)	Min Gain(dBi)	Avg. Gain(dBi)	Source Polar.
1		Axial Ratio	1561.00	3.60 / 359.40	-40.14 / 274.46	-3.92	CP





APRA1804G3Z

Request Samples (>)




Check Inventory (>)



18 x 18 x 4.0 mm RoHS/RoHS II Compliant MSL Level = 1

# **1602 MHz**



Patt	77105	Control of the second		CALL AND COLOR OF STREET	Min Gain(dBi)		Source Polar.
1		Axail Ratio	1602.00	4.55 / 359.40	-36.39 / 143.50	-2.97	CP





#### APRA1804G3Z

Request Samples



Check Inventory (>)



18 x 18 x 4.0 mm **RoHS/RoHS II Compliant** MSL Level = 1

## **Soldering Condition**

Soldering should be done in 3 seconds by a feed pin of maximum temperature +290 °C.

#### **Precautions**


- Soldering: Do not direct solder onto the silver electrode of the antenna pattern.
- Antenna pattern uses an Ag / Ni / Sn electrode. Do not use the patch antenna in a corrosive gaseous atmosphere for example sulfur gas, chlorine gas.
- Ultrasonic cleaning: Ultrasonic vibration may cause deterioration & destruction of the component. Please avoid ultrasonic cleaning.

## **Packaging Information**

Dimensions of the Carton: 330 x 280 x 254 mm

Number of pcs per Carton: 800

### DA Tray Packaging (25 pcs/Tray)







### APRA1804G3Z

Request Samples




Check Inventory (>)




18 x 18 x 4.0 mm RoHS/RoHS II Compliant MSL Level = 1

Inner Box Packaging: 200 pcs (8 Trays x 25 pcs)

Outer Box Packaging: 800 pcs (4 inner box x 200 pcs)





Unit: mm

ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.

