

# ANT-433-FPC-UFL-100 ✓ ACTIVE

TE Internal #: L9000120-01

Flexible PCB (FPC) Antenna, Multi Band, LPWAN / LoRaWAN,  
Internal/Embedded Mount, Adhesive, Solder, Omnidirectional,  
Single Port, Gain < 0 dBi

[View on TE.com >](#)



## Antennas



Wireless Application: **LoRaWAN, LPWAN**

Mounting Location: **Internal/Embedded**

Mounting Type: **Adhesive**

Antenna Termination: **Solder**

Antenna Type: **Flexible PCB (FPC)**

## Features

### Product Type Features

Antenna Product Type	Antenna
Antenna Termination	Solder

### Configuration Features

Antenna Style	Patch
Mounting Location	Internal/Embedded
Antenna Type	Flexible PCB (FPC)
Band Type	Multi Band
Port Configuration	Single Port

### Electrical Characteristics

VSWR (Max)	<4.1:1
Impedance	50 $\Omega$

### Signal Characteristics

Frequency Band	410 – 430 MHz
Nominal Frequency Range	410 – 470
Peak Gain	< 0 dBi

### Body Features

Product Weight	.6 g [.02116 oz]
----------------	------------------



### Mechanical Attachment

Polarization	Linear
Mounting Type	Adhesive

### Dimensions

Cable Length	.1 m[.33 ft]
Product Width	17 mm[.67 in]
Product Length	47 mm[1.85 in]
Product Height	.2 mm[.01 in]

### Operation/Application

Directionality	Omnidirectional
----------------	-----------------

### Industry Standards

Wireless Application	LoRaWAN, LPWAN
Primary Application	LoRaWAN, LPWAN

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2023 (235) Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the

product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

## Compatible Parts



TE Part # CONMHF1-SMD-G-T  
U.FL/MHF1 Jack 50 Ohm PCB Surface Mount



TE Part # CONMHF1-SMD-T  
U.FL/MHF1 Jack 50 Ohm PCB Surface Mount



TE Part # CONUFL001-SMD  
Conn UFL MHF Straight PCB Mount Jack



TE Part # CONUFL001-SMD-T  
U.FL/MHF1 Jack 50 Ohm PCB Surface Mount

## Customers Also Bought



TE Part #3-640441-2  
02P MTA100 CONN ASSY WHT



TE Part #1437566-4  
FSMSMTR=TACT SWITCH



TE Part #MS560702BA03-50  
MS5607-02BA SS CAP ALTIMETER T&R



TE Part #1676389-2  
RN 0805 5K62 0.1% 10PPM 1KRL



TE Part #1622796-2  
YR1 0.1% 100R



TE Part #5-2176304-2  
RP 1E 0.1W 34R 0.1% 25PPM 5K RL



TE Part #ANT-433-OC-LG-SMA  
Antenna Whip 433MHz Swivel SMA



TE Part #ANT-GNCP-C25L12100  
Antenna GNSS L1L2 25x25 LNA 1.13 UFL

## Documents

### Product Drawings

[Antenna FPC 433MHz 1.13 100 UFL](#)

English

### Datasheets & Catalog Pages

[Sub-6 Cellular LTE-5G NR Frequency Band Guide](#)

English

[Flexible Embedded 433 MHz Antenna](#)

English

[Virtual Antenna](#)

English



## Microsplat Ground Plane Optimization

English