


Radiall 狐

RIGHT ANGLE PLUG CRIMP TYPE CABLE 3.55/50 S

PAGE 1/3 ISSUE 11-09-15C SERIES BNC PART NUMBER R141195020



| COMPONENTS     | MATERIALS              | PLATING (μm)           |
|----------------|------------------------|------------------------|
| Body           | BRASS                  | NICKEL 2               |
| Center contact | BERYLLIUM COPPER,BRASS | GOLD 0.5 OVER NICKEL 2 |
| Outer contact  | -                      | -                      |
| Insulator      | PTFE                   |                        |
| Gasket         | SILICONE RUBBER        | NIOVEL 6               |
| Others parts   | BRASS                  | NICKEL 2               |
| -              | -                      | -                      |
| -              | -                      | <del>-</del>           |



# **Technical Data Sheet**

RIGHT ANGLE PLUG CRIMP TYPE CABLE 3.55/50 S

| PAGE <b>2/3</b> | ISSUE <b>11-09-15C</b> | SERIES BNC | PART NUMBER <b>R141195020</b> |
|-----------------|------------------------|------------|-------------------------------|
|-----------------|------------------------|------------|-------------------------------|

#### **PACKAGING**

| 100      | Contact us | Contact us |
|----------|------------|------------|
| Standard | Unit       | Other      |

## **ELECTRICAL CHARACTERISTICS**

Impedance 50 Ω Frequency 0-4 GHz **VSWR** 0,0000 x F(GHz) Maxi √F(GHz) dB Maxi Insertion loss 0.2 RF leakage 57 - F(GHz)) dB Maxi - ( Voltage rating 500 Veff Maxi Dielectric withstanding voltage 1000 Veff mini Insulation resistance 5000  $M\Omega$  mini

#### **MECHANICAL CHARACTERISTICS**

Center contact retention

Axial force - Mating End 27 N mini Axial force - Opposite end 27 N mini N.cm mini NA Torque

Recommended torque

Mating NA N.cm Panel nut NA N.cm Clamp nut N.cm 170 A/F clamp nut 8,0000 mm

Mating life 500 Cycles mini g

Weight 27,3820

### **ENVIRONMENTAL**

-65/+165 Operating temperature °C Hermetic seal NA Atm.cm3/s Panel leakage NA

#### **SPECIFICATION**

## CABLE ASSEMBLY

| Stripping | а | b | С  | d | е | f |
|-----------|---|---|----|---|---|---|
| mm        | 9 | 9 | 23 | 0 | 0 | 0 |

Assembly instruction:

Recommended cable(s)

#### GSC-03-81748-00

Characteristics indicated on this data sheet are those that can be achieved with the highest performance cable. Intrinsic limitations of the cable may diminish the performance of the assembly

Cable retention

- pull off 120 N mini - torque NA N.cm

#### **TOOLING**

| Part Number | Description                              | Hexagon        |  |
|-------------|--|----------------|--|
| R282293000  | CRIMPING TOOL M22520/5-01                |                |  |
| R282235011  | CRIMPING DIES M22520/5-11                | 5.41           |  |
| 282997      | POSITIONER FOR TOOL 282.291(M22520/1-13) | Red            |  |
| 282291      | CRIMPING TOOL M22520/1-01                | 2x4 pts(pos 7) |  |

# **OTHER CHARACTERISTICS**






RIGHT ANGLE PLUG CRIMP TYPE CABLE 3.55/50 S

PAGE **3/3** 

ISSUE 11-09-15C

SERIES BNC


# PART NUMBER **R141195020**



1

Slide onto the cable the heatshrink sleeve and the ferrule.

Strip the cable and cut the foil under the braid. Optionally, to facilitate the stripping of the inner cable, the length "a" could be stripped after crimping of the ferrule.




2

Slide the clamp nut onto the crimp sleeve.


Slide sub-assembly under the braid.

Slide ferrule over the braid against clamp nut.(In direction F) Crimp the ferrule with crimping tool + dies



3

The dielectric must be in the same plane as the face of the crimp sleeve. Cut the dielectric flush to crimp sleeve if it exceeds. Clean the dielectric side.



4

Slide the center contact onto the cable inner conductor against insulator.

Crimp the center contact with the crimping tool and the positioner.



5

Screw sub-assembly into the connector body. (recommended coupling see the connector TDS) Slide sleeve heatshrink over ferrule and put in the place as below.

